

2-Serial Module 6.0V 1.5F




FEATURES

Electric double layer capacitor
2 cells serially connected supercapacitor
Semi-permanent, quick charge and discharge than batteries
Suitable for smart meter or car driving recorder application
UL and ISO/TS certificated, RoHS compliant
Radial design with lead terminal type customized in 3 ways



DIMENSIONS



Dimensions in mm						
D +0.1 Max	W ± 1.0	L ± 1.5	d ± 0.1	P ± 0.2		
Φ8.5	17.0	22.0	Φ0.6	I: 4.7	O: 12.3	H: 8.5

This drawing is not to be scaled.

SPECIFICATIONS

Part Number	Rated Voltage, V_R (V)	Rated Capacitance (F)	AC ESR 1kHz (mΩ)	DC IR (mΩ)	Maximum Current (A)	Leakage Current (mA)	Stored Energy (J)	Dimension D x W x L (mm)	Weight (g)
VEC 6R0 155 QG-X	6.0	1.5	145.00	215.00	3.5	0.010	27.0	8.5 x 17.0 x 22.0	3.3

* X is variant type code such as I, O or H.

* Maximum Current: 1 second discharge to $\frac{1}{2} \cdot V_R$

* Leakage Current: After 72hours at V_R and 25 °C

Item	Characteristics	Remarks
Rated Voltage(V_R)	6.0V	
Capacitance Tolerance	-10 ~ +30%	
Operating Temperature ($T_{min} \sim T_{max}$)	-40 ~ +65 °C	$ \Delta cap \leq 30\%$ of initial value at 25 °C $ \Delta ESR \leq 100\%$ of specified value at 25 °C After 1,000 hours application of V_R at T_{max}
Storage Temperature	-40 ~ 70 °C	
Cycle Life	500,000 cycles	$ \Delta cap \leq 30\%$ of initial value at 25 °C $ \Delta ESR \leq 100\%$ of specified value at 25 °C Cycles from V_R to $\frac{1}{2} \cdot V_R$ under constant current at 25 °C
Shelf Life	2 years	$ \Delta cap \leq 10\%$ of initial value at 25 °C $ \Delta ESR \leq 50\%$ of specified value at 25 °C Without electrical charge under T_{max}