Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

82842 Multi-Conductor - Low Capacitance Computer and Computer P.O.S. Cable



For more Information please call

1-800-Belden1



General Description:

Low cap 24 AWG stranded (7x32) TC conductors, plenum, foam FEP insulation, twisted pairs, overall Beldfoil (100% coverage) + TC braid shield (90% coverage), 24 AWG stranded TC drain wire, Flamarrest® jacket.

jacket.												
	Characteristi	ics (Overa	all)									
Conductor AWG:	r											
	s AWG Strandir											
2	24 7x32	TC - Tinne	ed Cop	per								
Total N	umber of Condu	ictors:			4							
Insulation												
Insulation		Inculation	Mataria	-1	14/	all Thickness (in						
Teflon®	Insulation Trade Name Insulation Material Teflon® FEP - Foam Fluorinated Ethylene Propylene				all Thickness (ii 019							
Outer Shie Outer Shie	eld Material:											
Layer #	# Outer Shield T	Frade Name	Туре	Outer Shield Material		Coverage (%)						
1	Beldfoil®			Aluminum Foil-Polyester	Таре							
2			Braid	TC - Tinned Copper		90						
	eld Drain Wire A Stranding Drain		ictor M	latorial								
	-	Tinned Coppe		laterial								
Outer Jack Outer Jack	ket ket Material:											
Outer .	Jacket Trade Na	me Outer Ja	acket N	laterial	Nom	. Wall Thicknes						
Flamar	rrest®	LS PVC	- Low S	Smoke Polyvinyl Chloride	0.01	5						
Overall Ca	ble											
Overall	Nominal Diame	ter:			0.2	.73 in.						
Pair												
	r Code Chart:		_									
Numbe	Number Color 1 White/Blue & Blue/White											
2	White/Orange		hite									
				-								
	al Character		/erall)								
Operati	ing Temperature	Range:			-20	-20°C To +75°C						
Bulk Ca	able Weight:				38	lbs/1000 ft.						
Max. Re	Max. Recommended Pulling Tension:				56.700 lbs.							
Min. Be	end Radius/Mino	or Axis:			2.7	'50 in.						
A						. 11)						
	e Specificati e Standards &			cy Compliance (O	vera	all)						
	L) Specification		unai I	rogramo	CN	1P						
	(UL) Specificatio				CN							
	ective 2011/65/E	U (ROHS II):			Ye							
EU CE I	Mark:				Ye	s						
EU Dire	ective 2000/53/E	C (ELV):			Ye	S						
EU Dire	ective 2002/95/E	C (RoHS):			Ye	s						
EU RoH	IS Compliance I	Date (mm/dd	/уууу):	:	10/	01/2005						

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

82842 Multi-Conductor - Low Capacitance Computer and Computer P.O.S. Cable

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Flame Test	
UL Flame Test:	NFPA 262
CSA Flame Test:	FT6
Plenum/Non-Plenum	
Plenum (Y/N):	Yes
Non-Plenum Number:	9842
Electrical Characteristics (Overall)	
Nom. Characteristic Impedance:	
Impedance (Ohm)	
120	
Nom. Capacitance Conductor to Conductor:	
Capacitance (pF/ft)	
12	
Nom. Capacitance Cond. to Other Conductor & Shield:	
Capacitance (pF/ft) 22	
Nominal Velocity of Propagation:	
VP (%) 76	
Nom. Conductor DC Resistance:	
DCR @ 20°C (Ohm/1000 ft) 24	
Nominal Outer Shield DC Resistance:	
DCR @ 20°C (Ohm/1000 ft) 2.4	
Max. Operating Voltage - UL:	
Voltage 300 V RMS	
Max. Recommended Current:	
Current 3.2 Amps per conductor @ 25°C	

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
82842 8771000	1,000 FT	42.000 LB	NATURAL	С	2 PR #24 FFEP SH FLRST
82842 877500	500 FT	21.000 LB	NATURAL	С	2 PR #24 FFEP SH FLRST
82842 8775000	5,000 FT	210.000 LB	NATURAL		2 PR #24 FFEP SH FLRST

Notes:

C = CRATE REEL PUT-UP.

Revision Date: 08-15-2012 Revision Number: 2

© 2016 Belden, Inc All Rights Reserved.

All Rights Reserved. Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU ROHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is designed only as a general guide for the safe handling, storage, and any other operation of the product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden belares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).