

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000207](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: Mini-Fit® Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 18-24 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-5556-001 \(PDF\)](#)
[Product Specification PS-5556-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [5556](#)
 Application Power
 Crimp Quality Equipment Yes
 Overview [Mini-Fit Jr.™ Power Connectors](#)
 Packaging Alternative [39-00-0208 \(Loose\)](#)
 Product Name Mini-Fit®
 UPC 800754395991

Physical

Durability (mating cycles max) 30
 Gender Female
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.130/g
 Packaging Type Reel
 Plating min - Mating 2.540µm
 Plating min - Termination 1.270µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.30-3.10mm
 Wire Size AWG 18, 20, 22, 24
 Wire Size mm² N/A

Electrical


Current - Maximum per Contact 9.0A
 Voltage - Maximum 600V

Material Info

Engineering Number 5556-SP

Reference - Drawing Numbers

Packaging Specification PK-5556-001
 Product Specification PS-5556-001
 Sales Drawing SD-5556-SP*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

[5556 Series](#)

Mates With

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

Use With

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [5559](#) Mini-Fit Jr.™ Plug Housing, Dual Row