

Safety Data Sheet

NFPA	HMIS/WHMIS	PPE	Transport Symbol
10	Flammability 1 Health Hazard 1 Stability 0		

1. Product and Company Identification

Product Name: Tec Bond 232

Manufactured by: Power Adhesives Ltd

1 Lords Way

Basildon, Essex SS13 1TN United Kingdom

Telephone: (704) 334-2425

2. Hazards Identification

Contact with molten hot melt adhesives can cause severe burns.

Appearance: Water-White	Physical State: Solid	Odor: Slight

OSHA Regulatory Status: This material is not considered hazardous by the OSHA Hazard

Communication Standard (29 CFR 1910.1200)

Potential Health Effects:

Principle Routes of exposure: Eye Contact, Skin Contact, Inhalation

Acute Toxicity:

Eyes: May cause slight irritation. Contact with molten material may

cause severe burns.

Skin: May cause irritation and/or dermatitis. Contact with molten

material may cause severe burns.

Inhalation: Inhalation of fumes and/or dust may cause irritation of

respiratory system. Continuous breathing of vapors above

molten material may cause irritation.

Ingestion: Ingestion may cause stomach discomfort

Chronic Effects:

Chronic Toxicity: No Known Effect

Aggravated Medical Conditions: None Known

Environmental Hazard: See Section 12 for additional Information

3. Information on Compounded Ingredients

No known hazardous components.

Components	CAS-No	Weight %
Ethyl Vinyl Acetate	Not Available	Not Available

4. Fist Aid

General Advice: Hot melt adhesives pose virtually no hazards to health when

used in normal industrial practice, but because they are used in a molten state at high temperatures there is a risk of thermal burn. Skin contact with molten hot melt should be avoided and precautions taken against accidental splashes of adhesive. The use of hinged guards and the insulation of hot pipes, tanks, etc

minimize the risk of burns.

Inhalation: Noxious and irritating fumes may be released from heating hot

melts. Vapors given off during operation are not considered toxic, but if overheated chemical breakdown of the components may occur, releasing a complex mixture of organic materials, some of which may be toxic or irritant. Remove to fresh air, keeping patient warm and at rest. If breathing is irregular or stopped, administer artificial respiration. Give nothing by

mouth. Treat any irritation symptomatically. If unconscious or symptoms persist place in recovery position and seek medical

advice.

Skin Contact: Solid cold hot melt is harmless to the skin. Wash hands with

> soap and water. Skin affected by molten hot melt should be plunged into cold water immediately and left until the burning sensation subsides. If no tap is available have a bucket of clean cold water available. If coated with hot melt move fingers to prevent a tourniquet effect as it cools. Do not remove the adhesive when molten as it might remove skin to quite a depth leaving a raw wound. Even when solid remove with care as the above may occur. If difficult to remove, with medical approval, olive oil or liquid paraffin should be soaked into a cotton pad and placed over the affected area. This will slowly soften the adhesive into the pad. When hot melt is removed treat as a normal burn. In isolated circumstances an allergic reaction may occur and direct contact with the adhesive and its vapors should

be avoided.

Eye Contact: For solid treat as inert particles and irrigate copiously with clean

fresh water. For molten hot melt irrigate with cold water and

seek medical advice immediately.

Ingestion: If accidentally swallowed obtain immediate medical attention.

> Keep at rest. Do NOT induce vomiting. Give large quantities of water but never give anything by mouth to an unconscious

person.

5. Fire Fighting Measures

Flammable Properties: Non Flammable

Suitable Extinguishing Methods: Water Spray, dry chemical, carbon dioxide or foam

Hazardous Combustion Products: Carbon oxides

Protective Equipment and Precaution for first responders:

Wear self-contained breathing apparatus, MSHA/NIOSH

approved and full protective clothing

6. Accidental Release Measures

Personal Precautions: Wear protective gloves/clothing and eye protection

Methods for Containment: Prevent further leakage or spillage if safe to do so

Methods for Cleaning: Sweep up granules of solid material and place in a container for

disposal according to local regulations. Allow melt to cool and solidify. Scrape up and dispose of as above. Do not allow to

enter drains or water courses.

7. Handling and Storage

Handling: Do not heat hot melt above recommended temperatures.

Avoid overheating hot melts as this can give rise to excessive fuming indicating polymer breakdown and production of toxic

or irritant vapors.

Storage: Hot melts can be stored for indefinite periods, but stock

rotation is advised. Store in a dry, well ventilated place. Keep in original containers to avoid contamination with moisture and

other foreign bodies. Keep containers closed.

8. Exposure Controls/Personal Protection

Exposure guidelines: This product does not contain any hazardous material with

occupational exposure limits

Engineering Measures: Showers

Eyewash Stations

Ventilation Systems

Eye/Face Protection: Safety Glasses

Skin and Body Protection: Wear proper protective clothing

Respiratory Protection: If irritation is experienced, use NIOSH/MSHA approved

respiratory protection

9. Physical and Chemical Properties

Appearance: Water White

Physical State: Solid at room temperature

Flash Point: >492° F

Boiling Point: N/A

Freezing Point: N/A

Flammability: N/A

Odor: Slight

PH: N/A

Auto ignition Temp: N/A

Melting Point/Range: 189° F

Explosion Limits: N/A

Specific Gravity: .98

VOC Content: No VOC's

HAPS Data: No HAPS

10. Stability and Reactivity

Stability: Stable under normal recommended storage conditions

Incompatible Products: Strong oxidizing agents and other hot melt adhesives

Conditions to Avoid: None Known

Hazardous Decomposition Products: Carbon monoxide (CO) Carbon Dioxide (CO2)

Hazardous Reactions: Hazardous polymerization does not occur

11. Toxicological information		
Acute Toxicity:		
Product information:	Product does not present an acute toxicity hazard based on known or supplied information	
Irritation:	Repeated or prolonged exposure may cause eye or skin irritation	
Chronic Toxicity:		
Carcinogenicity:	Contains no ingredient listed as a carcinogen	
12. Ec	cological Information	
Eco toxicity:	The environmental impact of this product has not fully been investigated	
13. Disposal Considerations		
Waste Disposal Method:	Dispose of contents/container in accordance with local regulations	
14. Transport Information		
DOT:	Not Regulated	
TDG:	Not Regulated	
MEX:	Not Regulated	
IATA:	Not Regulated	
IMDG/IMO:	Not Regulated	

15. Regulatory Information

nternational Inventories:		
ΓSCA:	Complies	
OSL:	Complies	
EINECS:	Does Not Comply	
ENCS:	Does Not Comply	
ECSC:	Does Not Comply	
KECL:	Does Not Comply	
PICCS:	Does Not Comply	
AICS:	Does Not Comply	
JS Federal Regulations:	Sara 313 of title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.	
SARA 311/312 Hazard Categories:		
Acute Health Hazard:	No	
Chronic Health Hazard:	No	
Fire Hazard:	No	
Sudden Release of Pressure Hazard:	No	
Reactive Hazard:	No	
Clean Water Act:	This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)	
Clean Air Act Section 112 Hazardous Pollutants (HAPs) (see 40 CFR 61):		

Material Safety Data Sheet according to 91/155/EEC and ISO 11014 Tec Bond 232 Issue 4 Revised February 6, 2015

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of

the Clean Air Act Amendments of 1990.

CERCLA: This material, as supplied, does not contain any

substances regulated as hazardous substances under

the Comprehensive Environmental Response

Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional or stare level

pertaining to the releases of this material.

US State Regulations:

California Proposition 65: This product does not contain any Proposition 65

chemicals.

International Regulations:

Canada: This product has been classified in accordance with the

hazard criteria of the Controlled Products Regulations (CPR) and the MSDS contains all the information

required by the CPR.

WHMIS: Not determined

16. Other Information

Prepared by: Power Adhesives Quality and Technical Departments

Revision Date: 2-6-2015

The information contained in this safety data is based in the present state of knowledge and the current national legislation. It provides guidance on health, safety and environmental aspects of the product and should not be construed as any guarantee of technical performance or suitability for particular applications.

END OF DOCUMENT