

CorePro LEDspot MV

CorePro LEDspotMV 5-50W GU10 827 36D



CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

• General Information

Cap-Base	GU10
Bulb Shape	PAR16 [PAR 2 inch]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
B50L70	15000
Technical Type	5-50W

• Light Technical

Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	36 °
Luminous Intensity (Nom)	900 cd
Color Designation	Warm White (WW)
Rated Beam Angle	36 °
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	70 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux In 90° Cone (Rated)	350 lm

• Operating and Electrical

Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	50 W

Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V

• Temperature

T-Case Maximum (Nom)	85 °C
----------------------	-------

• Controls and Dimming

Dimmable	No
----------	----

• Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	5 kWh

• Product Data

Full product code	871869648598900
Order product name	CorePro LEDspotMV 5-50W GU10 827 36D
EAN/UPC - Product	8718696485989
Order code	929001220402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10


PHILIPS

CorePro LEDspot MV

Material Nr. (12NC) 929001220402

Net Weight (Piece) 0.038 kg

Dimensional drawing




GU10 230V 5W-50W 36D 2700K ND


Product	D	C
CorePro LEDspotMV 5-50W GU10 827 36D	50 mm	54 mm

Accent Lighting - Spots

1 x GU10 5W 2700K 36D ND

1 x 375 lm





© 2016 Philips Lighting Holding B.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2016, September 14
data subject to change