

Astro[®] Compact Scales **new**

A sleek portioning scale, easy to clean between weighing tasks



Features

- Color-coded keys facilitate quick recognition of the most frequently used buttons
- Large, grade 304 stainless steel pan allows swift cleaning
- Adjustable leveling feet help optimize setup
- Overload protection helps prevent damage to internal components
- Rugged stainless steel construction for ultimate durability
- Solid, one-piece construction is lightweight and easy to clean
- Operates with AC adapter (Included) or batteries (not included)
- Auto power-off to save energy
- External calibration allows for verification and adjustment with weights
- Splash-proof housing, keypad and display mean easy cleaning
- Colored LCD displays green when weighing and red at overload

General Specifications

- Weighing units: g, kg, lb, lb:oz, oz
- Interface: N/A
- Power Supply: 6VDC 500mA adapter / 2 x AAA batteries
- Display: Backlit LCD with 18mm-high digits
- Calibration: External calibration
- Housing: Stainless steel
- Operating Temperature: 0° to 40°C / 32° to 104°F

Model	Capacity	Readability	Pan Size
ASC 2001	2000g	0.1g	6.3"x7.1" / 160x180mm
ASC 4001	4000g	0.5g	6.3"x7.1" / 160x180mm
ASC 8000	8000g	1g	6.3"x7.1" / 160x180mm



Applications

- Weighing

Shipping Weight and Dimensions (wxdxh)

- Weight - 2lb / 1kg, Dim - 8.3"x9.5"x3.6" / 210x242x92mm