

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039296048](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Jr.™ Power Connectors](#)  
**Description:** Mini-Fit® Jr. Vertical Header, 4.20mm Pitch, Dual Row, 4 Circuits, without Snap-in Plastic Peg PCB Lock, Gold, Natural

**Documents:**

|   |   |
|---|---|
| <a href="#">3D Model</a>                                | <a href="#">Packaging Specification PK-5566 (PDF)</a>     |
| <a href="#">Drawing (PDF)</a>                           | <a href="#">Packaging Specification PK-5566-003 (PDF)</a> |
| <a href="#">Product Specification PS-5556-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>      |

**Agency Certification**


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |   |
|----------------|---|
| Product Family | PCB Headers   |
| Series         | 5566  |
| Application    | Power, Wire-to-Board  |
| Comments       | The 5566 header should be used with standard Mini-Fit® female terminals. If increased amperage of up to 13A per circuit is needed, please consider using the Mini-Fit® Plus HCS family <a href="#">45750</a> terminals with <a href="#">46015</a> headers; . See Molex Product specification PS-5666-001 for current de-rating information. |
| Overview       | <a href="#">Mini-Fit Jr.™ Power Connectors</a>  |
| Product Name   | Mini-Fit Jr.™   |
| UPC            | 800754374040  |

**Physical**

|                                |             |
|--------------------------------|-------------|
| Breakaway                      | No          |
| Circuits (Loaded)              | 4           |
| Circuits (maximum)             | 4           |
| Color - Resin                  | Natural     |
| Durability (mating cycles max) | 30          |
| First Mate / Last Break        | No          |
| Flammability                   | 94V-0       |
| Glow-Wire Compliant            | No          |
| Guide to Mating Part           | No          |
| Keying to Mating Part          | None        |
| Lock to Mating Part            | Yes         |
| Material - Metal               | Brass       |
| Material - Plating Mating      | Gold        |
| Material - Plating Termination | Matte Tin   |
| Material - Resin               | Nylon       |
| Net Weight                     | 1254.200/mg |
| Number of Rows                 | 2           |
| Orientation                    | Vertical    |
| PC Tail Length                 | 3.50mm      |
| PCB Locator                    | Yes         |
| PCB Retention                  | None        |
| PCB Thickness - Recommended    | 1.60mm      |
| Packaging Type                 | Bag         |
| Pitch - Mating Interface       | 4.20mm      |
| Pitch - Termination Interface  | 4.20mm      |
| Plating min - Mating           | 0.762µm     |
| Plating min - Termination      | 2.540µm     |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[5566 Series](#)

**Mates With**

[5557 Mini-Fit Jr.™ Receptacle Housing](#)

|                                |                 |
|--------------------------------|-----------------|
| Polarized to Mating Part       | Yes             |
| Polarized to PCB               | Yes             |
| Shrouded                       | Fully           |
| Stackable                      | No              |
| Surface Mount Compatible (SMC) | No              |
| Temperature Range - Operating  | -40°C to +105°C |
| Termination Interface: Style   | Through Hole    |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 9.0A |
| Voltage - Maximum             | 600V |

**Solder Process Data**

|  |      |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-free Process Capability                   | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 260  |

**Material Info**

|                    |                |
|--------------------|----------------|
| Engineering Number | 5566-04AGS-210 |
|--------------------|----------------|

**Reference - Drawing Numbers**

|                         |                      |
|-------------------------|----------------------|
| Packaging Specification | PK-5566, PK-5566-003 |
| Product Specification   | PS-5556-001          |
| Sales Drawing           | SD-5566-002          |

This document was generated on 09/20/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**