

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039000213

Status:

Active

Overview:

Mini-Fit Jr.™ Power Connectors

Description:

Mini-Fit® Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel

Documents:

Drawing (PDF)

Product Specification PS-5556-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Packaging Alternative	39-00-0214 (Loose)
Product Name	Mini-Fit®
UPC	800754319577
Physical	
Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.140/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	9.0A
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	5556-PBSP
Reference - Drawing Numbers	
Product Specification	PS-5556-001
Sales Drawing	SD-5556-SP*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

5556 Series

Mates With

5558 Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, 5566 , 5569

Use With

5557 Mini-Fit Jr.™ Receptacle Housing, 30067 Mini-Fit® TPA, 42474 Mini-Fit® BMI Panel Mount, 5559 Mini-Fit Jr.™ Plug Housing, Dual Row

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

FineAdjust™	<u>0639002900</u>
Applicator for	
Insulation OD	
1.65-2.05mm, 18-24	
AWG Wire	
Hand Crimp Tool for	<u>0638190900</u>
Male and Female	
Crimp Terminals,	
16-24 AWG Wire	
Extraction Tool	<u>0011030044</u>
FineAdjust™	<u>0639002600</u>
Applicator for	
Insulation OD	
2.50-2.95mm, 18-24	
AWG Wire	
FineAdjust™	<u>0639015600</u>
Applicator for	
Insulation OD	
1.90-2.30mm - 18-24	
AWG	
FineAdjust™	<u>0639023900</u>
Applicator for	
Insulation OD	
1.40-1.70mm - 18-24	
AWG	
FineAdjust™	<u>0639024900</u>
Applicator for	
Insulation OD	
2.30-2.60mm - 18-24	
AWG	
T2 Terminator™	<u>0639102600</u>
for insulation OD	
2.50-2.95mm - 18-24	
AWG	
T2 Terminator™ for	<u>0639102900</u>
insulation OD 1.65	
– 2.05mm – 18 – 24	
AWG	
T2 Terminator™	<u>0639124800</u>
for insulation OD	
2.50-2.95mm	
optimized for 18	
AWG only	
T2 Terminator™	<u>0639124900</u>
for insulation OD	
2.30-2.60mm - 18-24	
AWG	
FineAdjust™	<u>0639024800</u>
Applicator for	
Insulation OD	
2.50-2.95mm	
Optimized for 18	
AWG Only	
T2 Terminator™	<u>0639115600</u>
for insulation OD	
1.90-2.30mm - 18-24	
AWG	
T2 Terminator™	<u>0639123900</u>
for insulation OD	
1.40-1.70mm - 18-24	
AWG	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION