

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0330122001](#)
Status: **Active**
Overview: [MX150™ Sealed and Unsealed Connector System](#)
Description: [MX150™ Female Terminal Sealed, Tin Plating, 14 and 16 AWG, Right Reel Payoff](#)

Documents:

Drawing (PDF)	Application Specification AS-33012-002-FR (PDF)
Product Specification PS-33012-002 (PDF)	Test Summary TS-33012-002 (PDF)
Application Specification AS-33012-002 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33012-002-CH (PDF)	

General

Product Family	Crimp Terminals
Series	33012
Application	Power
Comments	For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers.
Crimp Quality Equipment Overview	Yes
Product Name	MX150™ Sealed and Unsealed Connector System
UPC	MX150™ 822350084222

Physical

Gender	Female
Grip Code	14
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.391/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	14, 16
Wire Size mm²	1.50

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-33012-002, AS-33012-002-CH, AS-33012-002-FR
Product Specification	PS-33012-002
Sales Drawing	SD-33012-002
Test Summary	TS-33012-002



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Compliant

Search Parts in this Series

[33012 Series](#)

Use With

[33472 Dual Row Housing](#), [33476 Hybrid Housing](#), [33471 Single Row Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ServiceGrade™	0640160133

Hand Crimp Tool for MX150™ Crimp Terminals, 14-22 AWG

Hand Crimp Tool, 14-16AWG	<u>0638115900</u>
Hand Crimp Tool, Metric 1.00 and 1.50	<u>0638116100</u>
Manual Extraction Tool	<u>0638131500</u>

This document was generated on 09/19/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION