NPN Silicon Epitaxial Transistor

These NPN Silicon Epitaxial transistors are designed for use in audio amplifier applications. The device is housed in the SOT–223 package, which is designed for medium power surface mount applications.

Features

- High Current: 1.0 A
- The SOT-223 package can be soldered using wave or reflow. The formed leads absorb thermal stress during soldering, eliminating the possibility of damage to the die
- Available in 12 mm Tape and Reel Use BCP56T1G to Order the 7 inch/1000 Unit Reel Use BCP56T3G to Order the 13 inch/4000 Unit Reel
- PNP Complement is BCP53T1G
- S and NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS (T_C = 25° C unless otherwise noted)

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V _{CEO}	80	Vdc
Collector-Base Voltage	V _{CBO}	100	Vdc
Emitter-Base Voltage	V _{EBO}	5	Vdc
Collector Current	۱ _C	1	Adc
Total Power Dissipation @ T _A = 25°C (Note 1) Derate above 25°C	P _D	1.5 12	W mW/°C
Operating and Storage Temperature Range	T _J , T _{stg}	-65 to 150	°C

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient (surface mounted)	R _{θJA}	83.3	°C/W
Maximum Temperature for Soldering Purposes Time in Solder Bath	TL	260 10	°C Sec

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


 Device mounted on a FR-4 glass epoxy printed circuit board 1.575 in x 1.575 in x 0.0625 in; mounting pad for the collector lead = 0.93 sq in.



ON Semiconductor®

www.onsemi.com

MEDIUM POWER NPN SILICON HIGH CURRENT TRANSISTOR SURFACE MOUNT



ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 2 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristics	Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS					
Collector–Base Breakdown Voltage $(I_C = 100 \ \mu Adc, I_E = 0)$	V _(BR) CBO	100	-	-	Vdc
Collector–Emitter Breakdown Voltage $(I_C = 1.0 \text{ mAdc}, I_B = 0)$	V _{(BR)CEO}	80	-	-	Vdc
Emitter–Base Breakdown Voltage ($I_E = 10 \ \mu Adc, I_C = 0$)	V _{(BR)EBO}	5.0	-	_	Vdc
Collector–Base Cutoff Current ($V_{CB} = 30 \text{ Vdc}, I_E = 0$)	I _{CBO}	-	-	100	nAdc
Emitter–Base Cutoff Current ($V_{EB} = 5.0 \text{ Vdc}, I_C = 0$)	I _{EBO}	-	-	10	μAdc
ON CHARACTERISTICS (Note 2)					
	6 0 6	25 40 63 100 25	- - - -	_ 250 160 250 _	-
Collector–Emitter Saturation Voltage $(I_C = 500 \text{ mAdc}, I_B = 50 \text{ mAdc})$	V _{CE(sat)}	-	-	0.5	Vdc
Base–Emitter On Voltage ($I_C = 500 \text{ mAdc}, V_{CE} = 2.0 \text{ Vdc}$)	V _{BE(on)}	-	-	1.0	Vdc
DYNAMIC CHARACTERISTICS					
Current–Gain – Bandwidth Product ($I_c = 10 \text{ mAdc}, V_{CE} = 5.0 \text{ Vdc}, f = 35 \text{ MHz}$)	f _T	-	130	_	MHz

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 2. Pulse Test: Pulse Width \leq 300 µs, Duty Cycle \leq 2.0%


ORDERING INFORMATION

Device	Marking	Package	Shipping [†]		
BCP56T1G	BH	SOT-223	1000 / Tape & Reel		
SBCP56T1G*		(Pb-Free)			
BCP56T3G	BH	SOT-223	4000 / Tape & Reel		
SBCP56T3G*		(Pb-Free)			
BCP56-10T1G	BH-10	SOT-223	1000 / Tape & Reel		
SBCP56-10T1G*		(Pb-Free)			
BCP56-10T3G	BH-10		4000 / Tape & Reel		
NSVBCP56-10T3G*		(Pb-Free)			
BCP56-16T1G	BH-16	SOT-223	1000 / Tape & Reel		
SBCP56-16T1G*		(Pb-Free)			
BCP56-16T3G	BH-16	SOT-223	4000 / Tape & Reel		
SBCP56-16T3G*		(Pb-Free)			


+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.
*S and NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and

PPAP Capable.

TYPICAL ELECTRICAL CHARACTERISTICS





TYPICAL ELECTRICAL CHARACTERISTICS



PACKAGE DIMENSIONS

SOT-223 (TO-261) CASE 318E-04 ISSUE N






NOTES: 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: INCH.

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	1.50	1.63	1.75	0.060	0.064	0.068
A1	0.02	0.06	0.10	0.001	0.002	0.004
b	0.60	0.75	0.89	0.024	0.030	0.035
b1	2.90	3.06	3.20	0.115	0.121	0.126
С	0.24	0.29	0.35	0.009	0.012	0.014
D	6.30	6.50	6.70	0.249	0.256	0.263
Е	3.30	3.50	3.70	0.130	0.138	0.145
е	2.20	2.30	2.40	0.087	0.091	0.094
e1	0.85	0.94	1.05	0.033	0.037	0.041
L	0.20			0.008		
L1	1.50	1.75	2.00	0.060	0.069	0.078
HE	6.70	7.00	7.30	0.264	0.276	0.287
θ		_			-	

PIN 1. BASE 10° 0° 2. COLLECTOR 10° 0° 3. EMITTER 4. COLLECTOR

10°

SOLDERING FOOTPRINT*



*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and the intervent and the intervent of the production of the property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under tights nor the rights of others. SCILLC products for any particular purpose, nor does y or other applications intended to support or sustain life, or for any other application in particular purpose, nor does or any or existent in the solution or use of any product or circuit, and convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product for any such unintended or unauthorized application. Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the de

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative