


CAMBLOCK PLUS

5mm Pitch Double Decker Rising Clamp Terminal Blocks

PCB
TERMINAL
BLOCKS

- Double interlocking mechanism for increased strength
- Double decker
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 2.5mm² (30-12AWG)
- Guided pin alignment
-  approved

CTBPDDVG



TYPE NO.	POLES	LENGTH
CTBPDDVG/2	4	12.5mm
CTBPDDVG/3	6	17.5mm
CTBPDDVG/4	8	22.5mm
CTBPDDVG/5	10	27.5mm
CTBPDDVG/6	12	32.5mm
CTBPDDVG/7	14	37.5mm
CTBPDDVG/8	16	42.5mm
CTBPDDVG/9	18	47.5mm
CTBPDDVG/10	20	52.5mm
CTBPDDVG/11	22	57.5mm
CTBPDDVG/12	24	62.5mm

SPECIFICATION

Rating	15A/300V
Insulation resistance	500M Ω /500V
Withstand Voltage	AC2000V/1min
Contact Resistance	20m Ω (max)
Working Temperature	-40°C to 105+°C
Mouldings	UL94-V0 Flame retardant PA66
Pin/Terminal	Tin plated brass
Rising Clamp	Brass, nickel plated
Screw/Torque	M2.5 Steel, zinc plated 0.4Nm
Recommended PCB hole size	ϕ 1.5mm

