



CAMBLOCK PLUS

5.08mm Pitch Low Profile Rising Clamp Terminal Blocks

PCB
TERMINAL
BLOCKS

- 2 & 3 pole double interlocking mechanism for increased strength
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 1.5mm² (26-16AWG)
- Guided pin alignment
- Captive screw
-  approved

CTBP0508



SPECIFICATION

Rating	8A/300V
Insulation resistance	500MΩ/500V
Withstand Voltage	AC2000V/1min
Contact Resistance	20mΩ (max)
Working Temperature	-40°C to 105°C
Mouldings	UL94-V0 Flame retardant PA66
Pin/Terminal	Tin plated brass
Rising Clamp	Brass, nickel plated
Screw/Torque	M2.5 Steel, zinc plated 0.4Nm
Recommended PCB hole size	ø1.3mm

TYPE NO.	POLES	LENGTH
CTBP0508/2	2	10.16mm
CTBP0508/3	3	15.24mm
CTBP0508/4	4	20.32mm
CTBP0508/5	5	25.4mm
CTBP0508/6	6	30.48mm
CTBP0508/7	7	35.56mm
CTBP0508/8	8	40.64mm
CTBP0508/9	9	45.72mm
CTBP0508/10	10	50.8mm
CTBP0508/11	11	55.88mm
CTBP0508/12	12	60.96mm

