



TapeCase Ltd.
1982 Lunt Ave, Elk Grove Village, IL 60007
phone: (847) 299-7880
fax: (847) 299-7804
www.tapecase.com
sales@tapecase.com

3M

Silicone-Free PTFE Film Tape

5498

Product Description 3M™ Silicone-Free PTFE Film Tape 5498 has a film backing with a silicone-free rubber adhesive.

Product Construction	Backing	Adhesive	Color
	Extruded PTFE (polytetrafluoroethylene)	Silicone-free rubber	Brown

Typical Physical Properties Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	48 oz./in. width (53 N/100 mm)	D-3330
Tensile Strength at Break:	19 lbs./in. width (332 N/100 mm)	D-3759
Elongation at Break:	105%	D-3759
Backing Thickness:	2.0 mils (0.05 mm)	D-3652
Total Tape Thickness:	4.0 mils (0.10 mm)	D-3652
Temperature Use Range:	40° to 300°F (4° to 149°C)	

- Features**
- Withstands autoclave cycles for several hours at temperatures up to 350°F (176°C) and 400°F (204°C) exposure for shorter periods.
 - Extruded PTFE film tape lies flatter than typical skived PTFE film tapes.

CAUTION: When PTFE film tape is exposed to temperatures above 400°F (204°C), small quantities of hazardous vapors may be released. INHALATION OF THESE VAPORS MAY BE HARMFUL OR MAY CAUSE RESPIRATORY TRACT IRRITATION. Do not heat or expose PTFE film tape to temperatures above 400°F (204°C).



TapeCase Ltd.
1982 Lunt Ave, Elk Grove Village, IL 60007
phone: (847) 299-7880
fax: (847) 299-7804
www.tapecase.com
sales@tapecase.com

Application Ideas

- Lining of composite bonding tool frames where there is concern of silicone contamination.
- Masking and bundling of composite parts prior to bonding operations where there is concern of silicone contamination.

Storage

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.