

No.	Murata Global P/N	Size (EIA)	TC Code	Rated Voltage	Cap.	Tol.	QTY
1	GRM0335C1HR10WA01	0201	COG	50Vdc	0.1pF	±0.05pF	20
2	GRM0335C1HR20BA01	0201	COG	50Vdc	0.2pF	±0.1pF	20
3	GRM0335C1HR30BA01	0201	COG	50Vdc	0.3pF	±0.1pF	20
4	GRM0335C1HR40BA01	0201	COG	50Vdc	0.4pF	±0.1pF	20
5	GRM0335C1HR50BA01	0201	COG	50Vdc	0.5pF	±0.1pF	20
6	GRM0335C1HR60BA01	0201	COG	50Vdc	0.6pF	±0.1pF	20
7	GRM0335C1HR70BA01	0201	COG	50Vdc	0.7pF	±0.1pF	20
8	GRM0335C1HR80BA01	0201	COG	50Vdc	0.8pF	±0.1pF	20
9	GRM0335C1HR90BA01	0201	COG	50Vdc	0.9pF	±0.1pF	20
10	GRM0335C1H1ROCA01	0201	COG	50Vdc	1.0pF	±0.25pF	100
11	GRM0335C1H1R2CA01	0201	COG	50Vdc	1.2pF	±0.25pF	20
12	GRM0335C1H1R5CA01	0201	COG	50Vdc	1.5pF	±0.25pF	20
13	GRM0335C1H1R8CA01	0201	COG	50Vdc	1.8pF	±0.25pF	20
14	GRM0335C1H2R2CA01	0201	COG	50Vdc	2.2pF	±0.25pF	20
15	GRM0335C1H2R7CA01	0201	COG	50Vdc	2.7pF	±0.25pF	20
16	GRM0335C1H3R3CA01	0201	COG	50Vdc	3.3pF	±0.25pF	20
17	GRM0335C1H3R9CA01	0201	COG	50Vdc	3.9pF	±0.25pF	20
18	GRM0335C1H4R7CA01	0201	COG	50Vdc	4.7pF	±0.25pF	20
19	GRM0335C1H5R6DA01	0201	COG	50Vdc	5.6pF	±0.5pF	20
20	GRM0335C1H6R8DA01	0201	COG	50Vdc	6.8pF	±0.5pF	20
21	GRM0335C1H8R2DA01	0201	COG	50Vdc	8.2pF	±0.5pF	20
22	GRM0335C1H100JA01	0201	COG	50Vdc	10pF	±5%	100
23	GRM0335C1H120JA01	0201	COG	50Vdc	12pF	±5%	20
24	GRM0335C1H150JA01	0201	COG	50Vdc	15pF	±5%	20
25	GRM0335C1H180JA01	0201	COG	50Vdc	18pF	±5%	20
26	GRM0335C1H220JA01	0201	COG	50Vdc	22pF	±5%	20
27	GRM0335C1H270JA01	0201	COG	50Vdc	27pF	±5%	20
28	GRM0335C1H330JA01	0201	COG	50Vdc	33pF	±5%	20
29	GRM0335C1H390JA01	0201	COG	50Vdc	39pF	±5%	20
30	GRM0335C1H470JA01	0201	COG	50Vdc	47pF	±5%	20
31	GRM0335C1H560JA01	0201	COG	50Vdc	56pF	±5%	20
32	GRM0335C1H680JA01	0201	COG	50Vdc	68pF	±5%	20
33	GRM0335C1H820JA01	0201	COG	50Vdc	82pF	±5%	20
34	GRM0335C1H101JA01	0201	COG	50Vdc	100pF	±5%	100
35	GRM0335C1H121JA01	0201	COG	50Vdc	120pF	±5%	20
36	GRM0335C1H151JA01	0201	COG	50Vdc	150pF	±5%	20
37	GRM0335C1H181JA01	0201	COG	50Vdc	180pF	±5%	20
38	GRM0335C1H221JA01	0201	COG	50Vdc	220pF	±5%	20
39	GRM0335C1E271JA01	0201	COG	25Vdc	270pF	±5%	20
40	GRM0335C1E331JA01	0201	COG	25Vdc	330pF	±5%	20
41	GRM0335C1E391JA01	0201	COG	25Vdc	390pF	±5%	20
42	GRM0335C1E471JA01	0201	COG	25Vdc	470pF	±5%	20
43	GRM0335C1E561JA01	0201	COG	25Vdc	560pF	±5%	20
44	GRM0335C1E681JA01	0201	COG	25Vdc	680pF	±5%	20
45	GRM0335C1E821JA01	0201	COG	25Vdc	820pF	±5%	20
46	GRM0335C1E102JA01	0201	COG	25Vdc	1000pF	±5%	100
47	GRM033R71H152KA12	0201	X7R	50Vdc	1500pF	±10%	20
48	GRM033R71E222KA12	0201	X7R	25Vdc	2200pF	±10%	20
49	GRM033R71E332KA12	0201	X7R	25Vdc	3300pF	±10%	20
50	GRM033R71E472KE14	0201	X7R	25Vdc	4700pF	±10%	20
51	GRM033R71A682KA01	0201	X7R	10Vdc	6800pF	±10%	20

52	GRM033R71E682KE14	0201	X7R	25Vdc	6800pF	±10%	20
53	GRM033R71E103KE14	0201	X7R	25Vdc	0.01μF	±10%	100
54	GRM033R61C153KE84	0201	X5R	16Vdc	0.015μF	±10%	20
55	GRM033R61C223KE84	0201	X5R	16Vdc	0.022μF	±10%	20
56	GRM033R61C333KE84	0201	X5R	16Vdc	0.033μF	±10%	20
57	GRM033R61C473KE84	0201	X5R	16Vdc	0.047μF	±10%	20
58	GRM033R61C683KE84	0201	X5R	16Vdc	0.068μF	±10%	20
59	GRM033R6YA104KE14	0201	X5R	35Vdc	0.1μF	±10%	100
60	GRM033R61A224ME90	0201	X5R	10Vdc	0.22μF	±20%	20
61	GRM033R60J474ME90	0201	X5R	6.3Vdc	0.47μF	±20%	20
62	GRM033R60J105ME11	0201	X5R	6.3Vdc	1μF	±20%	100
63	GRM033R60J225ME47	0201	X5R	6.3Vdc	2.2μF	±20%	20