

SAFETY DATA SHEET

SUPA-FIX - SUPABOND

Page: 1

Compilation date: 9/4/15

Revision No: 3

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: SUPA-FIX SUPABOND

Product code: SFSUPABDWE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

1.3. Details of the supplier of the safety data sheet

Company name: SUPA-FIX
UNIT 2, SHEPCOTE BUSINESS PARK
EUROPA DRIVE
SHEFFIELD
S9 1XT
ENGLAND

Tel: 0044 114 242 1030

Email: info@supa-fix.com

1.4. Emergency telephone number

Emergency tel: 0044 114 242 1030 (office hours only)

Company name: SUPA-FIX
UNIT 2, SHEPCOTE BUSINESS PARK
EUROPA DRIVE
SHEFFIELD
S9 1XT
ENGLAND

Tel: 0044 114 242 1030

Email: info@supa-fix.com

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: -: R52/53

Classification under CLP: Eye Irrit. 2: H319; Aquatic Chronic 3: H412; -: EUH208

[cont...]

SAFETY DATA SHEET

SUPA-FIX SUPABOND

Page: 2

Most important adverse effects: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Label elements:

Hazard statements: EUH208: Contains bis(1,2,2,6,6-pentamethyl-4-piperidyl) sebacate and methyl 1,2,2,6,6-pentamethyl-4-piperidyl sebacate., n-(2-aminoethyl)-3-aminopropyltrimethoxysilane.

May produce an allergic reaction.

H319: Causes serious eye irritation.

H412: Harmful to aquatic life with long lasting effects.

Signal words: Warning

Hazard pictograms: GHS07: Exclamation mark



Precautionary statements: P102: Keep out of reach of children.

P103: Read label before use.

P264: Wash hands thoroughly after handling.

P273: Avoid release to the environment.

P280: Wear eye protection and gloves.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+313: If eye irritation persists: Get medical advice.

P501: Dispose of contents to to standard waste.

Label elements under CHIP:

Hazard symbols: Symbol not required.

Risk phrases: R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases: S29: Do not empty into drains.

Precautionary phrases: Contains bis(1,2,2,6,6-pentamethyl-4-piperidyl) sebacate and methyl 1,2,2,6,6-pentamethyl-4-piperidyl sebacate., n-(2-aminoethyl)-3-aminopropyltrimethoxysilane. May produce an allergic reaction.

2.3. Other hazards

Other hazards: This product is not classified as hazardous according to current CHIP legislation

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

[cont...]

SAFETY DATA SHEET

SUPA-FIX SUPABOND

Page: 3

Hazardous ingredients:

TRIMETHOXY VINYLSILANE

EINECS	CAS	CHIP Classification	CLP Classification	Percent
220-449-8	2768-02-7	-: R10; Xn: R20	Acute Tox. 4: H332; Flam. Liq. 3: H226	1-10%

N-(2-AMINOETHYL)-3-AMINOPROPYLTRIMETHOXYSILANE

217-164-6	1760-24-3	Xi: R41; Sens.: R43; Xn: R20; N: R51/53	Eye Dam. 1: H318; Aquatic Chronic 2: H411; Acute Tox. 4: H332; Skin Sens. 1: H317	<1%
-----------	-----------	---	---	-----

BIS(1,2,2,6,6-PENTAMETHYL-4-PIPERIDYL) SEBACATE AND METHYL 1,2,2,6,6-PENTAMETHYL-4-PIPERIDYL SEBACATE.

-	-	Sens.: R43; N: R50/53	Skin Sens. 1: H317; Aquatic Acute 1: H400; Aquatic Chronic 1: H410	<1%
---	---	-----------------------	--	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

[cont...]

SAFETY DATA SHEET

SUPA-FIX SUPABOND

Page: 4

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not create dust.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.
Do not handle in a confined space. Avoid the formation or spread of dust in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency. Respiratory protective device with particle filter.

[cont...]

SAFETY DATA SHEET

SUPA-FIX SUPABOND

Page: 5

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Various

Odour: Barely perceptible odour

Evaporation rate: Negligible

Solubility in water: Insoluble

Also soluble in: Most organic solvents.

Viscosity: Highly viscous

Boiling point/range°C: >35

upper: N/A

Autoflammability°C: N/A

VOC g/l: 20

Flammability limits %: lower: N/A

Flash point°C: N/A

Relative density: 1.49

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

[cont...]

SAFETY DATA SHEET

SUPA-FIX SUPABOND

Page: 6

11.1. Information on toxicological effects

Hazardous ingredients:

BIS(1,2,2,6,6-PENTAMETHYL-4-PIPERIDYL) SEBACATE AND METHYL 1,2,2,6,6-PENTAMETHYL-4-PIPERIDYL SEBACATE.

ORAL	RAT	LD50	3230	mg/kg
------	-----	------	------	-------

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

TRIMETHOXY VINYLSILANE

Daphnia magna	-	21D NOEC 28	mg/l
Daphnia magna	48H EC50	169	mg/l
GREEN ALGA (Selenastrum capricornutum)	-	72H NOEC 25	mg/l
GREEN ALGA (Selenastrum capricornutum)	72H IC50	210	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	191	mg/l

N-(2-AMINOETHYL)-3-AMINOPROPYLTRIMETHOXYSILANE

Scenedesmus Subspicatus	72H EC50	126	mg/l
ZEBRAFISH (Brachydanio rerio)	96H LC50	597	mg/l

BIS(1,2,2,6,6-PENTAMETHYL-4-PIPERIDYL) SEBACATE AND METHYL 1,2,2,6,6-PENTAMETHYL-4-PIPERIDYL SEBACATE.

DESMODESMUS SUBSPICATUS	72H ErC50	1.68	mg/l
Daphnia magna	24H EC50	20	mg/l
FISH	96H LC50	0.97	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	7.9	mg/l

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

[cont...]

SAFETY DATA SHEET

SUPA-FIX SUPABOND

Page: 7

12.4. Mobility in soil

Mobility: Non-volatile.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Waste code number: 08 04 10

Disposal of packaging: Dispose of as normal industrial waste.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H317: May cause an allergic skin reaction.

H318: Causes serious eye damage.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

[cont...]

SAFETY DATA SHEET

SUPA-FIX SUPABOND

Page: 8

R10: Flammable.

R20: Harmful by inhalation.

R41: Risk of serious damage to eyes.

R43: May cause sensitisation by skin contact.

R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.