



Is Now Part of



ON Semiconductor®

**To learn more about ON Semiconductor, please visit our website at
www.onsemi.com**

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

74LVXC4245

8-Bit Dual Supply Configurable Voltage Interface Transceiver with 3-STATE Outputs

General Description

The LVXC4245 is a 24-pin dual-supply, 8-bit configurable voltage interface transceiver suited for PCMCIA and other real time configurable I/O applications. The V_{CCA} pin accepts a 5V supply level. The "A" Port is a dedicated 5V port. The V_{CCB} pin accepts a 3V-to-5V supply level. The "B" Port is configured to track the V_{CCB} supply level respectively. A 5V level on the V_{CC} pin will configure the I/O pins at a 5V level and a 3V V_{CC} will configure the I/O pins at a 3V level. This device will allow the V_{CCB} voltage source pin and I/O pins on the "B" Port to float when \overline{OE} is HIGH. This feature is necessary to buffer data to and from a PCMCIA socket that permits PCMCIA cards to be inserted and removed during normal operation.

Features


- Bidirectional interface between 5V and 3V-to-5V buses
- Control inputs compatible with TTL level
- Outputs source/sink up to 24 mA
- Guaranteed simultaneous switching noise level and dynamic threshold performance
- Implements patented EMI reduction circuitry
- Flexible V_{CCB} operating range
- Allows B Port and V_{CCB} to float simultaneously when \overline{OE} is HIGH
- Functionally compatible with the 74 series 245

Ordering Code:


Order Number	Package Number	Package Description
74LVXC4245WM	M24B	24-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide
74LVXC4245QSC	MQA24	24-Lead Quarter Size Outline Package (QSOP), JEDEC MO-137, 0.150" Wide
74LVXC4245MTC	MTC24	24-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

Logic Symbol



Connection Diagram



Pin Descriptions


Pin Names	Description
\overline{OE}	Output Enable Input
T/\overline{R}	Transmit/Receive Input
A_0 - A_7	Side A Inputs or 3-STATE Outputs
B_0 - B_7	Side B Inputs or 3-STATE Outputs

Truth Table

Inputs		Outputs
\overline{OE}	$\overline{T/R}$	
L	L	Bus B Data to Bus A
L	H	Bus A Data to Bus B
H	X	HIGH-Z State

H = HIGH Voltage Level
 L = LOW Voltage Level
 X = Immaterial

Logic Diagram



Absolute Maximum Ratings(Note 1)

Supply Voltage (V_{CCA}, V_{CCB})	-0.5V to +7.0V
DC Input Voltage (V_I) @ \overline{OE} , T/\overline{R}	-0.5V to $V_{CCA} + 0.5V$
DC Input/Output Voltage ($V_{I/O}$)	
@ A_n	-0.5V to $V_{CCA} + 0.5V$
@ B_n	-0.5V to $V_{CCB} + 0.5V$
DC Input Diode Current (I_{IK})	
@ \overline{OE} , T/\overline{R}	± 20 mA
DC Output Diode Current (I_{OK})	± 50 mA
DC Output Source or Sink Current (I_O)	± 50 mA
DC V_{CC} or Ground Current	
Per Output Pin (I_{CC} or I_{GND})	± 50 mA
and Max Current	± 200 mA
Storage Temperature Range (T_{STG})	-65°C to +150°C
DC Latch-Up Source or Sink Current	± 300 mA

Recommended Operating Conditions (Note 2)

Supply Voltage V_{CCA}	4.5V to 5.5V
V_{CCB}	2.7V to 5.5V
Input Voltage (V_I) @ \overline{OE} , T/\overline{R}	0V to V_{CCA}
Input/Output Voltage ($V_{I/O}$)	
@ A_n	0V to V_{CCA}
@ B_n	0V to V_{CCB}
Free Air Operating Temperature (T_A)	-40°C to +85°C
Minimum Input Edge Rate ($\Delta V/\Delta t$)	8 ns/V
V_{IN} from 30% to 70% of V_{CC}	
V_{CC} @ 3V, 4.5V, 5.5V	

Note 1: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 2: The A Port unused pins (inputs and I/O's) must be held HIGH or LOW. They may not float.

DC Electrical Characteristics

Symbol	Parameter		V _{CCA} (V)	V _{CCB} (V)	T _A = +25°C		T _A = -40°C to +85°C		Units	Conditions
					Typ	Guaranteed Limits				
V _{IHA}	Minimum HIGH Level Input Voltage	A _n	4.5	2.7		2.0	2.0	V	V _{OUT} ≤ 0.1V or ≥ V _{CC} - 0.1V	
		\overline{OE}	4.5	3.6		2.0	2.0			
		T/ \overline{R}	5.5	5.5		2.0	2.0			
		V _{IHB}	B _n	4.5	2.7		2.0			2.0
4.5	3.6				2.0	2.0				
4.5	5.5				3.85	3.85				
V _{ILA}	Maximum LOW Level Input Voltage	A _n	4.5	2.7		0.8	0.8	V	V _{OUT} ≤ 0.1V or ≥ V _{CC} - 0.1V	
		\overline{OE}	4.5	3.6		0.8	0.8			
		T/ \overline{R}	5.5	5.5		0.8	0.8			
		V _{ILB}	B _n	4.5	2.7		0.8			0.8
4.5	3.6				0.8	0.8				
4.5	5.5				1.65	1.65				
V _{OHA}	Minimum HIGH Level Output Voltage		4.5	3.0	4.49	4.4	4.4	V	I _{OUT} = -100 μA I _{OH} = -24 mA	
		4.5	3.0	4.25	3.86	3.76				
V _{OHB}			4.5	3.0	2.99	2.9	2.9	V	I _{OUT} = -100 μA I _{OH} = -12 mA I _{OH} = -24 mA I _{OH} = -12 mA I _{OH} = -24 mA I _{OH} = -24 mA	
			4.5	3.0	2.85	2.56	2.46			
			4.5	3.0	2.65	2.35	2.25			
			4.5	2.7	2.5	2.3	2.2			
			4.5	2.7	2.3	2.1	2.0			
			4.5	4.5	4.25	3.86	3.76			
V _{OLA}	Maximum LOW Level Output Voltage		4.5	3.0	0.002	0.1	0.1	V	I _{OUT} = 100 μA I _{OL} = 24 mA	
		4.5	3.0	0.21	0.36	0.44				
V _{OLB}			4.5	3.0	0.002	0.1	0.1	V	I _{OUT} = 100 μA I _{OL} = 24 mA I _{OL} = 12 mA I _{OL} = 24 mA I _{OL} = 24 mA	
			4.5	3.0	0.21	0.36	0.44			
			4.5	2.7	0.11	0.36	0.44			
			4.5	2.7	0.22	0.42	0.5			
			4.5	4.5	0.18	0.36	0.44			
I _{IN}	Maximum Input Leakage Current @ OE, T/ \overline{R}		5.5	3.6		±0.1	±1.0	μA	V _I = V _{CCA} , GND	
			5.5	5.5		±0.1	±1.0			

DC Electrical Characteristics (Continued)

Symbol	Parameter		V _{CCA} (V)	V _{CCB} (V)	T _A = +25°C		T _A = -40°C to +85°C		Units	Conditions
					Typ	Guaranteed Limits				
I _{OZA}	Maximum 3-STATE Output Leakage @ A _n		5.5 5.5	3.6 5.5		±0.5 ±0.5	±5.0 ±5.0		μA	V _I = V _{IL} , V _{IH} , \overline{OE} = V _{CCA} V _O = V _{CCA} , GND
I _{OZB}	Maximum 3-STATE Output Leakage @ B _n		5.5 5.5	3.6 5.5		±0.5 ±0.5	±5.0 ±5.0		μA	V _I = V _{IL} , V _{IH} , \overline{OE} = V _{CCA} V _O = V _{CCB} , GND
ΔI _{CC}	Maximum I _{CC} /Input	All Inputs	5.5	5.5	1.0	1.35	1.5		mA	V _I = V _{CC} - 2.1V
		B _n	5.5	3.6		0.35	0.5		mA	V _I = V _{CCB} - 0.6V
I _{CCA1}	Quiescent V _{CCA} Supply Current as B Port Floats		5.5	Open		8	80		μA	A _n = V _{CCA} or GND B _n = Open, \overline{OE} = V _{CCA} T/ \overline{R} = V _{CCA} , V _{CCB} = Open
I _{CCA2}	Quiescent V _{CCA} Supply Current		5.5 5.5	3.6 5.5		8 8	80 80		μA	A _n = V _{CCA} or GND B _n = V _{CCB} or GND \overline{OE} = GND, T/ \overline{R} = GND
I _{CCB}	Quiescent V _{CCB} Supply Current		5.5 5.5	3.6 5.5		5 8	50 80		μA	A _n = V _{CCA} or GND B _n = V _{CCB} or GND \overline{OE} = GND, T/ \overline{R} = V _{CCA}
V _{OLPA}	Quiet Output Maximum Dynamic		5.0 5.0	3.3 5.0		1.5 1.5			V	(Note 3) (Note 4)
V _{OLPB}	V _{OL}		5.0 5.0	3.3 5.0		0.8 1.5			V	(Note 3) (Note 4)
V _{OLVA}	Quiet Output Minimum Dynamic V _{OL}		5.0 5.0	3.3 5.0		-1.2 -1.2			V	(Note 3) (Note 4)
V _{OLVB}			5.0 5.0	3.3 5.0		-0.8 -1.2			V	(Note 3) (Note 4)
V _{IHDA}	Minimum HIGH Level Dynamic Input		5.0 5.0	3.3 5.0		2.0 2.0			V	(Note 3) (Note 5)
	Voltage		5.0 5.0	3.3 5.0		2.0 3.5			V	(Note 3) (Note 5)
V _{ILDA}	Maximum LOW Level Dynamic Input		5.0 5.0	3.3 5.0		0.8 0.8			V	(Note 3) (Note 5)
	Voltage		5.0 5.0	3.3 5.0		0.8 1.5			V	(Note 3) (Note 5)

Note 3: Worst case package.

Note 4: Max number of outputs defined as (n). Data inputs are driven 0V to V_{CC} level; one output at GND.

Note 5: Max number of Data Inputs (n) switching. (n-1) inputs switching 0V to V_{CC} level. Input-under-test switching: V_{CC} level to threshold (V_{IHD}), 0V to threshold (V_{ILD}), f = 1 MHz.

AC Electrical Characteristics

Symbol	Parameter	C _L = 50 pF V _{CCA} = 4.5V to 5.5V V _{CCB} = 4.5V to 5.5V					C _L = 50 pF V _{CCA} = 4.5V to 5.5V V _{CCB} = 2.7V to 3.6V					Units
		T _A = +25°C			T _A = -40°C to +85°C		T _A = +25°C			T _A = -40°C to +85°C		
		Min	Typ (Note 6)	Max	Min	Max	Min	Typ (Note 7)	Max	Min	Max	
t _{PHL}	Propagation Delay A to B	1.0	4.9	6.5	1.0	7.0	1.0	5.5	7.5	1.0	8.0	ns
t _{PLH}	Delay A to B	1.0	4.0	5.5	1.0	6.0	1.0	5.0	7.0	1.0	7.5	
t _{PHL}	Propagation Delay B to A	1.0	4.7	6.5	1.0	7.0	1.0	5.6	7.5	1.0	8.0	ns
t _{PLH}	Delay B to A	1.0	3.9	5.0	1.0	5.5	1.0	4.3	6.0	1.0	6.5	
t _{PZL}	Output Enable Time \overline{OE} to B	1.0	5.6	7.5	1.0	8.0	1.0	6.7	9.0	1.0	10.0	ns
t _{PZH}	Time \overline{OE} to B	1.0	5.7	7.5	1.0	8.0	1.0	6.9	9.5	1.0	10.0	
t _{PZL}	Output Enable Time \overline{OE} to A	1.0	7.4	9.0	1.0	10.0	1.0	8.0	10.0	1.0	11.0	ns
t _{PZH}	Time \overline{OE} to A	1.0	6.1	7.5	1.0	8.5	1.0	6.3	8.0	1.0	8.5	
t _{PHZ}	Output Disable Time \overline{OE} to B	1.0	4.8	7.0	1.0	7.5	1.0	6.0	9.0	1.0	9.5	ns
t _{PLZ}	Time \overline{OE} to B	1.0	3.8	5.5	1.0	6.0	1.0	4.2	6.5	1.0	7.0	
t _{PHZ}	Output Disable Time \overline{OE} to A	1.0	3.4	5.5	1.0	6.0	1.0	3.4	5.5	1.0	6.0	ns
t _{PLZ}	Time \overline{OE} to A	1.0	2.9	4.5	1.0	5.0	1.0	2.9	5.0	1.0	5.5	
t _{OSHL}	Output to Output Skew (Note 8)		1.0	1.5		1.5		1.0	1.5		1.5	ns
t _{OSLH}	Data to Output											

Note 6: Typical values at V_{CCA} = 5V, V_{CCB} = 5V @ 25°C.

Note 7: Typical values at V_{CCA} = 5V, V_{CCB} = 3.3V @ 25°C.

Note 8: Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW (t_{OSHL}) or LOW-to-HIGH (t_{OSLH}). Parameter guaranteed by design.

Capacitance

Symbol	Parameter		Typ	Units	Conditions
C _{IN}	Input Capacitance		4.5	pF	V _{CC} = Open
C _{I/O}	Input/Output Capacitance		10	pF	V _{CCA} = 5V, V _{CCB} = 3.3V
C _{PD}	Power Dissipation Capacitance (Note 9)	A→B	45	pF	V _{CCA} = 5V
		B→A	50	pF	V _{CCB} = 3.3V

Note 9: C_{PD} is measured at 10 MHz.

Power Up Considerations

To insure the system does not experience unnecessary I_{CC} current draw, bus contention, or oscillations during power up, the following guidelines should be adhered to (refer to Table 1):

- Power up the control side of the device first. This is the V_{CCA}.
- \overline{OE} should ramp with or ahead of V_{CCA}. This will help guard against bus contention.
- The Transmit/Receive control pin (T/R) should ramp with V_{CCA}, this will ensure that the A Port data pins are con-

figured as inputs. With V_{CCA} receiving power first, the A I/O Port should be configured as inputs to help guard against bus contention and oscillations.

- A side data inputs should be driven to a valid logic level. This will prevent excessive current draw.

The above steps will ensure that no bus contention or oscillations, and therefore no excessive current draw occurs during the power up cycling of these devices. These steps will help prevent possible damage to the translator devices and potential damage to other system components.



TABLE 1. Low Voltage Translator Power Up Sequencing Table

Device Type	V _{CCA}	V _{CCB}	T/R	\overline{OE}	A Side I/O	B Side I/O	Floatable Pin Allowed
74LVXC4245	5V (power up 1st)	2.7V to 5.5V configurable	ramp with V _{CCA}	ramp with V _{CCA}	logic 0V or V _{CCA}	outputs	yes, V _{CCB} and B I/O's w/ \overline{OE} HIGH


Please reference Application Note AN-5001 for more detailed information on using Fairchild's LVX Low Voltage Dual Supply CMOS Translating Transceivers.

The diagram illustrates the architecture of the PCMCIA 2.0 JEIDA 4.1 Compatible Controller. On the left, a vertical double-headed arrow represents the **ISA BUS (IEEE P996)**. The controller is a central block with two bidirectional connections to the ISA bus. To its right, a horizontal double-headed arrow represents the **SD(0:15)** interface. Below the controller, a dashed box labeled **OPTIONAL** encloses the **SLOT 0** and **SLOT 1** components. Each slot contains a vertical stack of components labeled **L**, **V**, **X**, **C**, **4**, **2**, **4**, and **5**. The **SLOT 0** component is connected to **5V V_{CC}** and **V_{CCB}**. The **SLOT 1** component is connected to **5V V_{CC}** and **3V V_{CC}**. The **POWER SWITCHES** are located between the controller and the slots. The **SD(0:15)** interface is shown as a horizontal double-headed arrow at the bottom.

The V_{CCA} pin on the LVXC4245 must always be tied to a 5V power supply. This voltage connection provides internal references needed to account for variations in V_{CCB}. When connected as in the block diagram above, the LVXC4245 meets all the voltage and current requirements of the ISA bus standard (IEEE P996).



Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com