

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039000060](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Jr.™ Power Connectors](#)  
**Description:** [Mini-Fit® Female Crimp Terminal, Tin \(Sn\) over Phosphor Bronze, 18-24 AWG, Bag](#)

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-54452-006 (PDF)</a>
<a href="#">Product Specification PS-51010-003 (PDF)</a>	<a href="#">Product Specification PS-54452-007 (PDF)</a>
<a href="#">Product Specification PS-51010-004 (PDF)</a>	<a href="#">Product Specification PS-54849-004 (PDF)</a>
<a href="#">Product Specification PS-51045-003 (PDF)</a>	<a href="#">Product Specification PS-5556-001 (PDF)</a>
<a href="#">Product Specification PS-52252-001 (PDF)</a>	<a href="#">Product Specification PS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-54111-001 (PDF)</a>	<a href="#">Packaging Specification PK-5556-003 (PDF)</a>
<a href="#">Product Specification PS-54111-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<a href="#">5556</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr.™ Power Connectors</a>
Packaging Alternative	<a href="#">39-00-0059 (Reel)</a>
Product Name	Mini-Fit®
UPC	800753584679

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.127/g
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

**Electrical**


Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	5556PBTL
--------------------	----------

**Reference - Drawing Numbers**

Packaging Specification	PK-5556-003
Product Specification	PS-51010-003, PS-51010-004, PS-51045-003, PS-52252-001, PS-54111-001, PS-54111-002, PS-54452-006, PS-54452-007, PS-54849-004, PS-5556-001, PS-5556-002, RPS-51045-002, RPS-52034-001, RPS-54111-002, RPS-54111-004, RPS-54111-005, RPS-54269-004, RPS-5557-001, RPS-5557-027, RPS-5557-054
Sales Drawing	SD-5556****



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[5556 Series](#)

**Mates With**

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

**Use With**

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [5559](#) Mini-Fit Jr.™ Plug Housing, Dual Row

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Hand Crimp Tool for [0638190900](#)  
Male and Female  
Crimp Terminals,  
16-24 AWG Wire  
Extraction Tool [0011030044](#)

**Japan**

<b>Description</b>	<b>Product #</b>
Handtool (Straight Action)	<a href="#">0570225500</a>
Hand Crimp Tool	<a href="#">0570265000</a>

This document was generated on 09/20/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**