

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022041151](#)
Status: **Active**
Overview: [Mini-Latch™ Wire-to-Board System](#)
Description: Mini-Latch™ Wire-to-Board Header, Vertical, with Friction Ramp, 15 Circuits, Tin (Sn) Plating

Documents:

3D Model	Product Specification PS-5051-005 (PDF)
Drawing (PDF)	Product Specification PS-51191-002 (PDF)
Product Specification PS-5045-001 (PDF)	Packaging Specification SPK-5045-001 (PDF)
Product Specification PS-5045-002 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-5051-001 (PDF)	

Agency Certification


UL E29179

General

Product Family	PCB Headers
Series	5045
Application	Signal, Wire-to-Board
Overview	Mini-Latch™ Wire-to-Board System
Product Name	Mini-Latch™
UPC	800753740815

Physical

Breakaway	No
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1492.000/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[5045](#) Series

Mates With

KK® 2.50mm Housings [51191](#) , [5051](#)

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	5045-15A
Reference - Drawing Numbers	
Packaging Specification	SPK-5045-001
Product Specification	PS-5045-001, PS-5045-002, PS-5051-001, PS-5051-005, PS-51191-002, RPS-5045-001, RPS-51191-007
Sales Drawing	SD-5045-NA

This document was generated on 09/30/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION