

# **Product Termination Notification**

Product Group: Aluminum Capacitors/Sep-30-2016/PCN-AC-903-2016 Rev 0

## **Product Termination TVA1720 electrolytic capacitors**

#### **DESCRIPTION OF CHANGE:**

Termination of production of a special design TVA capacitor

**CLASSIFICATION OF CHANGE:** Product Termination with no replacement

**REASON FOR CHANGE:** No more availability of raw material. Tool to manufacture the disk used for this capacitor is not available any longer. Any LTB orders will be subjected to minimums and additional price for tooling.

**EXPECTED INFLUENCE ON QUALITY/RELIABILTY/PERFORMANCE:** Not applicable

**PRODUCT CATAGORY:** Aluminum Electrolytic Capacitors

PART NUMBERS/SERIES/FAMILIES AFFECTED: TVA1720 - Spec sheet attached

VISHAY BRAND(s): Vishay Sprague

TIME SCHEDULE:

Last Time order date: October 30th, 2016 Last Time shipment date: December 30th, 2016

**SAMPLE AVAILABILITY:** Not applicable

**PRODUCT IDENTIFICATION:** Not applicable

**QUALIFICATION DATA:** Not applicable

This PTN is considered approved, without further notification, unless we receive specific customer concerns before October 30th, 2016 or as specified by contract.

**ISSUED BY:** Walter Bonomo

For further information, please contact your regional Vishay office.

CONTACT INFORMATION:

**The Americas**Vishay

Europe
Vishay

Vishay E

Walter Bonomo Gerald Tats
Tel. +1 704 924 5188 Tel. +43 463
Fax. +1 704 924 5158 Fax. +43 46

Walter.Bonomo@Vishay.com

Vishay BCcomponents Austria Gerald Tatschl Tel. +43 463 3834-314 Fax. +43 463 3834-301

Gerald.Tatschl@Vishay.com

**Asia Pacific** 

Vishay Boon Hooi Tan Tel. +65 6780 7759 Fax. +65 6780 7749

BoonHooi.Tan@Vishay.com

Vishay Intertechnology, Inc.



Dmax

Wa

Lmax

PVC

SLEEVE

## **ALUMINUM CAPACITORS**

#### **Electrical and Mechanical Specifications**

**Product Type:** Large Axial (Radial Lead Configuration)

P/N:

TVA1720

Capacitance:

200 μF

Tolerance:

-10% / +50%

Voltage:

0-450 VDC

ESR:

 $0.980\,\Omega$  max.

DF:

Wс

14.78 % max.

DC Leakage:

1800.0 µA max. after 5 min.

charge at rated voltage

Ripple@120Hz:

1.284 Amps @ 85°C

20kHz

Amps @ 85°C

Sleeving:

**BLUE PVC** 

Marking:

**SPRAGUE** ATOM ®

TVA1720

RED 200UF 450VDC

BLACK NEG. 85C DATE CODE

Comments: LEADS ARE FLEXIBLE INSULATED 8"

WIRES. BLACK=NEG.(-), RED=POS.(+)

Figure	Dimensions	
G	0.040 in.	1.02 mm
D	1.375 in. nom.	34.93 mm nom.
Dmax	1.405 in. max.	35.69 mm max.
L	4.125 in. nom.	104.78 mm nom.
Lmax	4.203 in. max.	106.76 mm max.
Wa	8.000 in. nom.	203.20 mm nom.
Wb	0.600 in. nom.	15.24 mm nom.
Wc	8.000 in. nom.	203.20 mm nom.

FULL DESCRIPTOR P/N:

54D201F450MD6BA1720V.

NOTE: max. dimensions include sleeving thickness

Drawn by: R. Lam

Date: August 1, 2011





Vishay

#### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

### **Material Category Policy**

Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

This datasheet is subject to change without notice. THE PRODUCT DESCRIBED HEREIN AND THIS DATASHEET ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <a href="https://www.vishay.com/doc?91000">www.vishay.com/doc?91000</a>

Revision: 13-Jun-16 Document Number: 91000