

TENMA™

76-1672 76-1674 76-1476

Insulator	: Polyamide (Nylon)
Jack Body	: Brass, Nickel Plated
Nut	: Brass, Nickel Plated, 2 Pieces
Voltage Rating	: 1,200V AC/DC
Current Rating	: 36A Max.
Temperature	: -20°C to +80°C
Max. panel Thickness	: 0.6" (15.2mm)

Description	Colour	Part Number
Binding Post, 36A, M6, Turret	Black	76-1672
	Red	76-1674
	Blue	76-1476

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk
www.mcmelectronics.com

