

# PC Based Oscilloscope 60MHz, 2 Channels Arbitrary Wave Form Generator



## Specifications:

	Model	72-10179
Horizontal	Analog Channels	2
	Bandwidth	60MHz (-3dB)
	Rise Time	5.8ns
	Real-time Sampling Rate	200MSPS
	Time Base Range	5ns/div~1,000s/div (1-2-5 sequences)
	Time Base Precision	±50ppm
Vertical	Input Impedance	Resistance: 1MΩ ; Capacitance: 25pF
	Input Sensitivity	10mV/div to 5V/div
	Input Coupling	AC, DC and GND
	Vertical Resolution	8 bits
	Memory Depth (Sample Points)	10K-16M/CH
	Maximum Input	400V (DC+AC Peak)
Trigger	Source	CH1, CH2, EXT
	Mode	Edge, Pulse, Video, Alternative
X-Y Mode	X-Axis Input	CH1/CH2
	Y-Axis Input	CH1/CH2
	Phase Shift	Max. 3 degree
Cursors and Measurement	Voltage Measurement	Vpp, Vamp, Vmax, Vmin, Vtop, Vmid, Vbase, Vavg, Vrms, Vcrms, Preshoot, Overshoot
	Time Measurement	Frequency, Period, Rise Time, Fall Time, Positive Width, Negative Width, Duty Cycle
	Cursors Measurement	Horizontal, Vertical, Track, Auto Measure Modes
	Waveform Signal Process	., -, ×, ÷, FFT, Invert
Others	Auto Set	yes
	Voltage Range	10mV to 5V/div @ × 1 probe 100mV to 50V/div @ × 10 probe 1V to 500V/div @ × 100 probe 10V to 5,000V/div @ × 1,000 probe 100V to 50,000V/div @ × 10,000 probe 200mV to 100V/div @ 20:1



# PC Based Oscilloscope 60MHz, 2 Channels Arbitrary Wave Form Generator



	Model	72-10179
Others	Cursor	Time/frequency difference, voltage difference
	Current Range	CC65(20A), CC65(60A), CC650, CC1100
	Cursor	Time/frequency difference, Voltage difference
	FFT	Rectangular, Hanning, Hamming, Blackman Window
	Math	Addition, Subtraction, Multiplication, Division
	Interface	USB 2.0 (LAN, WIFI Optional)
Arbitrary Wave Form Generator Mode	Waveform Frequency	DC ~ 25MHz
	DAC	2k ~ 200MHz adjustable
	Frequency Resolution	0.1%
	Waveform Depth	4KSa
	Vertical Resolution	12bit
	Frequency Stability	<30ppm
	Wave Amplitude	±3.5V Max.
	Output Impedance	50Ω
	Output Current	50mA Ipeak = 50mA
	Harmonic Distortion	-50dBc(1kHz), -40dBc(10kHz)
Power Source	8 - 36V Wide range of input voltage, suitable for vehicle power test	
Mechanics	Dimension	255mm × 190mm × 45mm
	Weight	1kg

## Part Number Table

Description	Part Number
2 Channels Oscilloscope, Arbitrary Wave Form Generator	72-10179

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.



# Palm Size Digital Multimeter **TENMA™**



## Specifications:

Basic Functions	Range	Best Accuracy
DC Voltage	200mV/2,000mV/20V/200V/250V	±(0.5%+2)
AC Voltage	200V/250V	±(1.2%+10)
DC Current	2,000µA/20mA/200mA/10A	±(1%+2)
Resistance	200Ω/2,000Ω/20kΩ/200kΩ/20MΩ/200MΩ	±(0.8%+2)

## Special Functions

Display Count		2,000
Manual Range		√
Square Wave Output		√
Diode		√
Continuity Buzzer		√
Low Battery Indication		√
Data Hold		√
LCD Backlight		√
Input Protection		√
Input Impedance for DCV	Around :10MΩ	√

## General Characteristics

Power	9V Battery (6F22)
LCD Size	48mm×16mm
Product Colour	Orange and Grey
Product Net Weight	180g (Including Holster)
Product Size	130mm × 73.5mm × 35mm
Standard Accessories	Battery, Test Lead, Holster

## Part Number Table

Description	Part Number
Palm Size Digital Multimeter	72-7770A

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.