

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 105 °C	STORAGE TEMPERATURE RANGE	-10 °C TO 50 °C (PACKED CONDITION)
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)
	CURRENT	0.5 A (note)	APPLICABLE CABLE	t=0.3±0.05mm, GOLD PLATING

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

ELECTRICAL CHARACTERISTICS				
CONTACT RESISTANCE	AC 20 mV MAX (1 KHz) , 1 mA .	50 mΩ MAX. INCLUDING FPC, FFC BULK RESISTANCE (L=8mm)	X	X
INSULATION RESISTANCE	100 V DC.	500 MΩ MIN.	X	X
VOLTAGE PROOF	150 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	X

MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	20 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
VIBRATION	FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, - m/s ² FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 50 mΩ MAX.	X	-
SHOCK	981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
FPC RETENTION FORCE	MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.30mm AT INITIAL CONDITION.)	DIRECTION OF INSERTION: 0.4N × n MIN. (n:NUMBER OF CONTACTS)	X	-

ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -40→+15 to +35→+105→15 to +35°C TIME 30→ 2 to 3 → 30→ 2 to 3 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2°C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.		X	-
DAMP HEAT, CYCLIC	EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES, TOTAL 240 h.	① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
DRY HEAT	EXPOSED AT 105±2 °C, 96 h.	① CONTACT RESISTANCE: 50 mΩ MAX.	X	-
COLD	EXPOSED AT -40±3°C, 96 h.	② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
CORROSION SALT MIST	EXPOSED AT 35±2°C, 5 % SALT WATER SPRAY FOR 96 h.	① CONTACT RESISTANCE: 50 mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	X	-
SULPHUR DIOXIDE [JIS C 60068-2-42]	EXPOSED AT 40±2 °C, RELATIVE HUMIDITY 80±5% , 25±5 ppm FOR 96 h.		X	-
HYDROGEN SULPHIDE [JIS C 60068-2-43]	EXPOSED AT 40±2 °C, RELATIVE HUMIDITY 80±5% , 10 TO 15 ppm FOR 96 h.		X	-

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
0				

REMARK	APPROVED	NF. MIYAZAKI	15.10.17
	CHECKED	HS. SAKAMOTO	15.10.17
	DESIGNED	RT. IKEDA	15.10.17
	DRAWN	RN. IIDA	15.10.15

Unless otherwise specified, refer to IEC 60512.

Note	QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC-156370-05-05
HRS	SPECIFICATION SHEET	PART NO.	FH28E-*S-0.5SH (05)
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL586

Nov.1.2016 Copyright 2016 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING (MAX 2 CYCLES) PEAK TMP. 250 °C MAX . REFLOW TMP. OVER 230 °C WITHIN 60 sec. PRE-HEAT 150 TO 200°C FOR 90 TO 120 sec. 2) SOLDERING IRONS : TMP. 350±10°C FOR 5±1 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 235±5°C FOR IMMERSION DURATION, 2±0.5 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	x	—

(note)

WHEN THE SAME VALUE OF CURRENT ARE APPLIED TO ALL CONTACTS AT THE SAME TIME IN ONCE, SET THE CURRENT TO THE 70 % OF THE RATED CURRENT VALUE.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-156370-05-05		
HRS	SPECIFICATION SHEET		PART NO.	FH28E-*S-0. 5SH (05)		
	HIROSE ELECTRIC CO., LTD.		CODE NO	CL586		2/2