

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0553585029

Status:


Active

Overview:

CompactFlash™

Description:

1.27mm Pitch CF Card Header- Right Angle, Surface Mount Top Mounting for Type I and II Cards



Series image - Reference only

Documents:	
3D Model	Product Specification PS-55546-005 (PDF)
Drawing (PDF)	Product Specification PS-55546-006 (PDF)
Product Specification PS-55358-012 (PDF)	Packaging Specification SPK-55358-001 (PDF)
Product Specification PS-55358-013 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Memory Card Sockets
Series	55358
Overview	CompactFlash™
Product Name	CompactFlash
Style	Guide and Holder
UPC	822348180691
Physical	
Card Detection Switch	N/A
Card Entry Location	Front
Circuits (Loaded)	50
Durability (mating cycles max)	10000
Ejector Button Side	N/A
Flammability	94V-0
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin
Net Weight	3780.078/mg
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Temperature Range - Operating	-20°C to +90°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	100V AC (RMS)
Voltage Key	3.3V, 5.0V
Material Info	
Reference - Drawing Numbers	
Packaging Specification	SPK-55358-001
Product Specification	PS-55358-012, PS-55358-013, PS-55546-005, PS-55546-006
Sales Drawing	SD-55358-014

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/21/2016 (20 June 2016)	
Halogen-Free	
Status	
Low-Halogen	
Need more information on product environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series
55358 Series
Mates With
67003 , 67114 , Industry Standard CF Card
Use With
55356 Ejector, 55364 Ejector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION