

EELP 18, EILP 18
Core set (with and without clamp recess)

Series/Type: B66283G, B65804, B66283K, B66284, B66453G, B66453K

Date: March 2016

© EPCOS AG 2016. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



ELP 18/4/10

Core and accessories (with clamp recess)

B66283, B65804

ELP 18/4/10

Core set EELP 18

Combination: ELP 18/4/10 with ELP 18/4/10

■ To IEC 62317-9


■ Delivery mode: single units

Magnetic characteristics (per set)

 Σ I/A = 0.62 mm⁻¹ I_e = 24.3 mm A_e = 39.3 mm² A_{min} = 38.9 mm²

 $V_{\rm e}^{11111} = 955 \, \rm mm^3$

Approx. weight 4.8 g/set



18±0.35

FEK0515-R

Ungapped

Material	A _L value nH	μ_{e}	P _V W/set	Ordering code (per piece)
N49	1900 ±25%	930	< 0.25 (50 mT, 500 kHz, 100 °C)	B66283G0000X149
N92	2050 ±25%	1010	< 0.66 (200 mT, 100 kHz, 100 °C)	B66283G0000X192
N87	2600 ±25%	1270	< 0.60 (200 mT, 100 kHz, 100 °C)	B66283G0000X187
N97	2670 ±25%	1314	< 0.47 (200 mT, 100 kHz, 100 °C)	B66283G0000X197

Calculation factors (for formulas, see "E cores: general information") EELP 18:

Material	Relationship air gap – A _L v		Calculation o	f saturation cu	rrent	
	K1 (25 °C)	K2 (25 °C)	K3 (25 °C)	K4 (25 °C)	K3 (100 °C)	K4 (100 °C)
N87	71.1	-0.773	124	-0.796	104	-0.873


Validity range: K1, K2: 0.10 mm < s < 1.50 mm

K3, K4: $50 \text{ nH} < A_L < 500 \text{ nH}$

Clamp

Ordering code per piece, 2 pieces required

Ordering code: B65804P2204X000





ELP 18/4/10 with I 18/2/10

Core and accessories (with clamp recess)

B66283


Core set EILP 18 **Combination:** ELP 18/4/10 with I 18/2/10

- To IEC 62317-9
- Delivery mode: single units

Magnetic characteristics (per set)

 $\Sigma I/A = 0.51 \text{ mm}^{-1}$ = 20.3 mm $= 39.5 \text{ mm}^2$ $A_{min} = 38.9 \text{ mm}^2$ $= 802 \text{ mm}^3$

Approx. weight 4.1 g/set



Ungapped

Material	A _L value nH	μ_{e}	P _V W/set	Ordering code (per piece)
N49	2100 ±25%	860	< 0.20 (50 mT, 500 kHz, 100 °C)	B66283G0000X149 (ELP core) B66283K0000X149 (I core)*
N92	2300 ±25%	930	< 0.55 (200 mT, 100 kHz, 100 °C)	B66283G0000X192 (ELP core) B66283K0000X192 (I core)*
N87	2900 ±25%	1180	< 0.50 (200 mT, 100 kHz, 100 °C)	B66283G0000X187 (ELP core) B66283K0000X187 (I core)*
N97	3000 ±25%	1230	< 0.42 (200 mT, 100 kHz, 100 °C)	B66283G0000X197 (ELP core) B66283K0000X197 (I core)*

^{*} Plate-type tool type



ELP 18/4/10 with I 18/2/10

Core and accessories (with clamp recess)

B66284

Calculation factors (for formulas, see "E cores: general information") **EILP 18:**

Material	Relationship air gap – A _L v		Calculation o	f saturation cu	rrent	
	K1 (25 °C)	K2 (25 °C)	K3 (25 °C)	K4 (25 °C)	K3 (100 °C)	K4 (100 °C)
N87	77.4	-0.774	129	-0.796	107	-0.873


Validity range: K1, K2: 0.10 mm < s < 1.50 mm

K3, K4: $50 \text{ nH} < A_L < 500 \text{ nH}$

Clamp

Ordering code per piece, 2 pieces required

Ordering code: B66284F2204X000





ELP 18/4/10

Core (without clamp recess)

B66453

Core set EELP 18

Combination: ELP 18/4/10 with ELP 18/4/10

■ To IEC 62317-9

■ Delivery mode: single units

Magnetic characteristics (per set)

 $\Sigma I/A = 0.62 \text{ mm}^{-1}$


 $I_{e} = 24.3 \text{ mm}$

 $A_{p} = 39.3 \text{ mm}^2$

 $A_{min} = 38.9 \text{ mm}^2$

 $V_e = 955 \text{ mm}^3$

Approx. weight 4.8 g/set



ELP 18/4/10

Ungapped

Material	A _L value nH	μ_{e}	P _V W/set	Ordering code (per piece)
N49	1900 ±25%	930	< 0.25 (50 mT, 500 kHz, 100 °C)	B66453G0000X149
N92	2050 ±25%	1010	< 0.66 (200 mT, 100 kHz, 100 °C)	B66453G0000X192
N87	2600 ±25%	1270	< 0.60 (200 mT, 100 kHz, 100 °C)	B66453G0000X187
N97	2650 ±25%	1300	< 0.50 (200 mT, 100 kHz, 100 °C)	B66453G0000X197

Calculation factors (for formulas, see "E cores: general information") **EELP 18:**

Material		Relationship between air gap – A _L value		Calculation of saturation current			
	K1 (25 °C)	K2 (25 °C)	K3 (25 °C)	K4 (25 °C)	K3 (100 °C)	K4 (100 °C)	
N87	71.1	-0.773	124	-0.796	104	-0.873	

Validity range: K1, K2: 0.10 mm < s < 1.50 mm

K3, K4: $50 \text{ nH} < A_L < 500 \text{ nH}$



ELP 18/4/10 with I 18/2/10

Core (without clamp recess)

B66453

Core set EILP 18 Combination:


ELP 18/4/10 with I 18/2/10

- To IEC 62317-9
- Delivery mode: single units

Magnetic characteristics (per set)

 Σ I/A = 0.51 mm⁻¹ I_e = 20.3 mm A_e = 39.5 mm² A_{min} = 38.9 mm² V_e = 802 mm³

Approx. weight 4.1 g/set



FEK0536-E-E

Ungapped

Material	A _L value nH	μ_{e}	P _V W/set	Ordering code (per piece)
N49	2100 ±25%	860	< 0.20 (50 mT, 500 kHz, 100 °C)	B66453G0000X149 (ELP core) B66453K0000X149 (I core)*
N92	2300 ±25%	930	< 0.55 (200 mT, 100 kHz, 100 °C)	B66453G0000X192 (ELP core) B66453K0000X192 (I core)*
N87	2900 ±25%	1180	< 0.50 (200 mT, 100 kHz, 100 °C)	B66453G0000X187 (ELP core) B66453K0000X187 (I core)*
N97	3000 ±25%	1230	< 0.42 (200 mT, 100 kHz, 100 °C)	B66453G0000X197 (ELP core) B66453K0000X197 (I core)*

^{*} Plate-type tool type

Calculation factors (for formulas, see "E cores: general information") EILP 18:

Material	Relationship between air gap – A _L value		Calculation of saturation current			
	K1 (25 °C)	K2 (25 °C)	K3 (25 °C)	K4 (25 °C)	K3 (100 °C)	K4 (100 °C)
N87	77.4	-0.774	129	-0.796	107	-0.873

Validity range: K1, K2: 0.10 mm < s < 1.50 mm

K3, K4: $50 \text{ nH} < A_L < 500 \text{ nH}$



Cautions and warnings

Mechanical stress and mounting

Ferrite cores have to meet mechanical requirements during assembling and for a growing number of applications. Since ferrites are ceramic materials one has to be aware of the special behavior under mechanical load.

As valid for any ceramic material, ferrite cores are brittle and sensitive to any shock, fast changing or tensile load. Especially high cooling rates under ultrasonic cleaning and high static or cyclic loads can cause cracks or failure of the ferrite cores.

For detailed information see chapter "Definitions", section 8.1.

Effects of core combination on A_L value

Stresses in the core affect not only the mechanical but also the magnetic properties. It is apparent that the initial permeability is dependent on the stress state of the core. The higher the stresses are in the core, the lower is the value for the initial permeability. Thus the embedding medium should have the greatest possible elasticity.

For detailed information see chapter "Definitions", section 8.2.

Heating up

Ferrites can run hot during operation at higher flux densities and higher frequencies.

NiZn-materials

The magnetic properties of NiZn-materials can change irreversible in high magnetic fields.

Processing notes

- The start of the winding process should be soft. Else the flanges may be destroyed.
- Too strong winding forces may blast the flanges or squeeze the tube that the cores can not be mounted any more.
- Too long soldering time at high temperature (>300 °C) may effect coplanarity or pin arrangement.
- Not following the processing notes for soldering of the J-leg terminals may cause solderability problems at the transformer because of pollution with Sn oxyd of the tin bath or burned insulation of the wire. For detailed information see chapter "Processing notes", section 8.2.
- The dimensions of the hole arrangement have fixed values and should be understood as a recommendation for drilling the printed circuit board. For dimensioning the pins, the group of holes can only be seen under certain conditions, as they fit into the given hole arrangement. To avoid problems when mounting the transformer, the manufacturing tolerances for positioning the customers' drilling process must be considered by increasing the hole diameter.

Display of ordering codes for EPCOS products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications and the website of EPCOS, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.epcos.com/orderingcodes.



Symbols and terms

Symbol	Meaning	Unit
A	Cross section of coil	mm ²
A_{e}	Effective magnetic cross section	mm ²
Al	Inductance factor; $A_L = L/N^2$	nH
A_{L1}	Minimum inductance at defined high saturation ($\triangleq \mu_a$)	nH
A_{min}	Minimum core cross section	mm ²
A_N	Winding cross section	mm ²
A_R	Resistance factor; $A_R = R_{Cu}/N^2$	$\mu\Omega = 10^{-6} \Omega$
В	RMS value of magnetic flux density	Vs/m ² , mT
ΔΒ	Flux density deviation	Vs/m ² , mT
Ê	Peak value of magnetic flux density	Vs/m ² , mT
ΔÂ	Peak value of flux density deviation	Vs/m ² , mT
B_DC	DC magnetic flux density	Vs/m ² , mT
B _R	Remanent flux density	Vs/m ² , mT
B _S	Saturation magnetization	Vs/m ² , mT
C_0	Winding capacitance	F = As/V
CDF	Core distortion factor	mm ^{-4.5}
DF	Relative disaccommodation coefficient DF = d/μ_i	
d	Disaccommodation coefficient	
E_a	Activation energy	J
f	Frequency	s ^{−1} , Hz
f _{cutoff}	Cut-off frequency	s−1, Hz
f _{max}	Upper frequency limit	s ^{−1} , Hz
f _{min}	Lower frequency limit	s−1, Hz
f _r	Resonance frequency	s ^{−1} , Hz
f_{Cu}	Copper filling factor	
g	Air gap	mm
Н	RMS value of magnetic field strength	A/m
Ĥ	Peak value of magnetic field strength	A/m
H_{DC}	DC field strength	A/m
H _c	Coercive field strength	A/m
h	Hysteresis coefficient of material	10 ⁻⁶ cm/A
h/μ_i^2	Relative hysteresis coefficient	10 ⁻⁶ cm/A
1	RMS value of current	Α
I_{DC}	Direct current	Α
î	Peak value of current	Α
J	Polarization	Vs/m ²
k	Boltzmann constant	J/K
k ₃	Third harmonic distortion	
k _{3c}	Circuit third harmonic distortion	
L	Inductance	H = Vs/A



Symbols and terms

Symbol	Meaning	Unit
ΔL/L	Relative inductance change	Н
L_0	Inductance of coil without core	Н
L_H	Main inductance	Н
L_p	Parallel inductance	Н
L _{rev}	Reversible inductance	Н
L _s	Series inductance	Н
l _e	Effective magnetic path length	mm
I _N	Average length of turn	mm
N	Number of turns	
P_{Cu}	Copper (winding) losses	W
P _{trans}	Transferrable power	W
P_V	Relative core losses	mW/g
PF	Performance factor	
Q	Quality factor (Q = $\omega L/R_s$ = 1/tan δ_l)	
R	Resistance	Ω
R_{Cu}	Copper (winding) resistance (f = 0)	Ω
R _h	Hysteresis loss resistance of a core	Ω
ΔR_h	R _h change	Ω
R _i	Internal resistance	Ω
R _p	Parallel loss resistance of a core	Ω
R_s^r	Series loss resistance of a core	Ω
R _{th}	Thermal resistance	K/W
R_V	Effective loss resistance of a core	Ω
S	Total air gap	mm
Т	Temperature	°C
ΔT	Temperature difference	K
T_C	Curie temperature	°C
t	Time	s
t _v	Pulse duty factor	
tan δ	Loss factor	
tan δ_L	Loss factor of coil	
tan δ_r	(Residual) loss factor at H \rightarrow 0	
tan $\delta_{\rm e}$	Relative loss factor	
$tan \delta_h$	Hysteresis loss factor	
tan δ/μ _i	Relative loss factor of material at H \rightarrow 0	
U	RMS value of voltage	V
Û	Peak value of voltage	V
V _e	Effective magnetic volume	mm ³
Z	Complex impedance	Ω
Z _n	Normalized impedance $ Z _n = Z / N^2 \times \varepsilon (I_e / A_e)$	Ω/mm



Symbols and terms

Symbol	Meaning	Unit
α	Temperature coefficient (TK)	1/K
α_{F}	Relative temperature coefficient of material	1/K
α_{e}	Temperature coefficient of effective permeability	1/K
ε_{r}	Relative permittivity	
Φ	Magnetic flux	Vs
1	Efficiency of a transformer	
ηΒ	Hysteresis material constant	mT-1
٦i	Hysteresis core constant	$A^{-1}H^{-1/2}$
λ_{S}	Magnetostriction at saturation magnetization	
u	Relative complex permeability	
10	Magnetic field constant	Vs/Am
^l a	Relative amplitude permeability	
^l app	Relative apparent permeability	
ı _e	Relative effective permeability	
ι_{i}	Relative initial permeability	
ι _p '	Relative real (inductive) component of $\overline{\mu}$ (for parallel components)	
ι _p "	Relative imaginary (loss) component of $\overline{\mu}$ (for parallel components)	
lr	Relative permeability	
^l rev	Relative reversible permeability	
ls'	Relative real (inductive) component of $\overline{\mu}$ (for series components)	
ι _s "	Relative imaginary (loss) component of $\overline{\mu}$ (for series components)	
^l tot	Relative total permeability	
	derived from the static magnetization curve	
)	Resistivity	Ω m $^{-1}$
EI/A	Magnetic form factor	mm ⁻¹
Cu	DC time constant $\tau_{Cu} = L/R_{Cu} = A_L/A_R$	s
Œ	Angular frequency; ω = 2 Π f	s ⁻¹

All dimensions are given in mm.





Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
 - We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, Alu-X, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PQSine, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, TFAP, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.