

## 7937A Multi-Conductor - DataTuff® Waterblocked Cate 5e Cable



For more Information  
please call

1-800-Belden1



### General Description:

24 AWG solid bare copper conductors, twisted bonded pairs, polyolefin insulation, polymer gel waterblocked, inner LLPE jacket, overall Beldfoil shield (100% coverage), 24 AWG stranded TC drain wire, industrial grade sunlight- and oil-resistant LLPE jacket.

### Usage (Overall)

**Suitable Applications:** Industrial Ethernet Cable, Harsh Environments, 100MHz Category 5e, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, RS-422, CMX - Outdoor, RJ-45 Compatible, Noisy Environments

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
4	24	Solid	BC - Bare Copper	0.508

**Total Number of Conductors:** 8

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PO - Polyolefin	0.229	0.965

#### Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (mm)
LLPE - Linear Low Density Polyethylene	5.461

#### Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
LLPE - Linear Low Density Polyethylene	0.508

**Outer Jacket Ripcord:** No

#### Overall Cable

**Overall Nominal Diameter:** 7.010 mm

#### Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

### Mechanical Characteristics (Overall)

**Storage Temperature Range:** -40°C To +85°C

**Installation Temperature Range:** -25°C To +75°C

**Operating Temperature Range:** -40°C To +75°C

**Bulk Cable Weight:** 49.111 Kg/Km

## 7937A Multi-Conductor - DataTuff® Waterblocked Cate 5e Cable

Max. Recommended Pulling Tension:	177.928 N
Min. Bend Radius/Minor Axis:	69.850 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II):	Yes
Other Standards:	ISO/IEC 11801 ed 2.1 (2008) Class D
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 5e

#### Applicable Patents:

Country	www.belden.com/p
---------	------------------

#### Suitability

Suitability - Outdoor:	Yes
Suitability - Burial:	Yes - Telcordia, IEC, ICEA
Sunlight Resistance:	Yes
Oil Resistance:	Yes
Non-halogenated:	Yes

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Electrical Characteristics (Overall)

#### Nom. Mutual Capacitance:

Capacitance (pF/m)	49.215
--------------------	--------

Maximum Capacitance Unbalance (pF/100 m):	330
---	-----

#### Nominal Velocity of Propagation:

VP (%)	70
--------	----

#### Maximum Delay:

Delay (ns/100 m)	538 @ 100MHz
------------------	--------------

#### Max. Delay Skew:

Delay Skew (ns/100 m)	45
-----------------------	----

#### Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)	9.38
------------------------	------

#### Max. Operating Voltage - UL:

Voltage	300 V RMS
---------	-----------

#### Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)	3
--------------------------	---

### Electrical Characteristics-Premise (Overall)

#### Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	65.3	62.3	63.0	60.0	20.0	23
4	4.1	56.3	53.3	51.0	49.0	23.0	23.0
8	5.8	51.8	48.8	46.0	43.0	24.5	24.5

## 7937A Multi-Conductor - DataTuff® Waterblocked Cate 5e Cable

10	6.5	50.3	47.3	43.0	41.0	25.0	25.0
16	8.2	47.3	44.3	39.0	36.0	25.0	25.0
20	9.3	45.8	42.8	36.5	33.5	25.0	25.0
25	10.4	44.3	41.3	33.9	30.9	24.3	24.3
31.25	11.7	42.9	39.9	31.0	28.0	23.6	23.6
62.5	17.0	38.4	35.4	22.0	19.0	21.5	21.5
100	22.0	35.3	32.3	14.0	11.0	20.1	20.1

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	63.8	60.8
4	100 ± 15	100 ± 15	51.7	48.7
8	100 ± 15	100 ± 15	45.7	42.7
10	100 ± 15	100 ± 15	43.8	40.8
16	100 ± 15	100 ± 15	39.7	36.7
20	100 ± 15	100 ± 15	37.7	34.7
25	100 ± 15	100 ± 15	35.8	32.8
31.25	100 ± 15	100 ± 15	33.9	30.9
62.5	100 ± 15	100 ± 15	27.8	24.8
100	100 ± 15	100 ± 15	23.8	20.8

### Notes (Overall)

**Notes:** Operating temperatures are subject to length de-rating. Cable passes -40°C Cold Bend per UL 1581. Sequential marking at two foot intervals. Polymer gel waterblocking material.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7937A 0101000	1,000 FT	38.000 LB	BLACK		4 PR #24 P0 GEL LLDPO FS LLDPO

Revision Number: 1    Revision Date: 03-11-2014

© 2016 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.