

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0330013004](#)
Status: **Active**
Overview: [MX150™ Sealed and Unsealed Connector System](#)
Description: [MX150™ Female Terminal Sealed, Gold Plating, 16, 18 and 20 AWG, Left Reel Payoff](#)

Documents:

Drawing (PDF)	Application Specification AS-33012-002-FR (PDF)
Product Specification PS-33012-002 (PDF)	Test Summary TS-33001-002 (PDF)
Application Specification AS-33012-002 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33012-002-CH (PDF)	



Series image - Reference only

General

Product Family	Crimp Terminals
Series	33001
Application	Power
Comments	Left Reel Payoff, Small Polarization Rib
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	MX150™ Sealed and Unsealed Connector System
Product Name	MX150™
UPC	822350084178

Physical

Gender	Female
Grip Code	18
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Unplated
Net Weight	0.435/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.54mm max.
Wire Size AWG	18, 20
Wire Size mm²	0.75-1.00

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-33012-002, AS-33012-002-CH, AS-33012-002-FR
Product Specification	PS-33012-002
Sales Drawing	SD-33012-002
Test Summary	TS-33001-002

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Compliant

Search Parts in this Series

[33001](#) Series

Use With

[33472](#) Dual Row Housing. [33476](#) Hybrid
Housing. [33471](#) Single Row Housing