


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0022011042
Status: Active
Overview: KK® Interconnect System - Molex
Description: 2.50mm Pitch KK® Wire-to-Board Housing, Female, Friction Lock, for 2759/5159 Crimp Terminals, 4 Circuits



Documents:	
3D Model	Product Specification PS-5045-004 (PDF)
Drawing (PDF)	Product Specification PS-5046-004 (PDF)
Product Specification PS-5045-001 (PDF)	Product Specification PS-5051-003 (PDF)
Product Specification PS-5045-002 (PDF)	Product Specification PS-5051-004 (PDF)
Product Specification PS-5045-003 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	5051
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK®
UPC	800753593923
Physical	
Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	547.600/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Material Info	
Engineering Number	5051-04
Reference - Drawing Numbers	
Product Specification	PS-5045-001, PS-5045-002, PS-5045-003, PS-5045-004, PS-5046-004, PS-5051-003, PS-5051-004
Sales Drawing	SD-5051-001

EU ELV Not Relevant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - ED/21/2016 (20 June 2016)	
Halogen-Free Status Low-Halogen	
Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	
China ROHS ELV	Green Image Not Relevant

Search Parts in this Series 5051 Series
Mates With 5045 Vertical Header, 5046 Right Angle Header
Use With 2759 , 5159

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION