

PARATHOM MR11 20 30° 3.7 W/827 GU4

PARATHOM MR11 12 V | Low-voltage LED reflector lamps MR11 with retrofit pin base



Areas of application

- As a downlight for marking walkways, doors, stairs, etc.
- Shops selling jewellery, glassware or ceramic goods
- Outdoor applications only in suitable luminaires
- Directional light sources
- Museums
- Hospitality
- Shops

Product benefits

- Very low energy consumption
- Extremely long life
- Robust against vibrations
- No UV and near-IR radiation in the light beam
- Efficient generation of white light
- Professional thermal management
- Ideal for economical spotlighting
- Excellent price/performance ratio

Product features

- Professional LED lamps for line voltage
- Not dimmable
- Color temperature: 2,700 K
- Good color rendering ($R_a \geq 80$) and color stability throughout the life of the lamp
- Base: GU4
- Lifetime: up to 15,000 h



Product datasheet

- Mercury-free lamps
- High color consistency

Technical data

Electrical data

Rated wattage	3.70 W
Nominal wattage	3.70 W
Nominal voltage	12.0 V
Claimed equiv. conventional lamp power	20 W
Operating frequency	50...60 Hz
Power factor λ	> 0.50


Photometrical data

Luminous intensity	550 cd
Nominal luminous flux	200 lm
Rated luminous flux	200 lm
Color temperature	2700 K
Color rendering index Ra	80
Light color (designation)	Warm White
Standard deviation of color matching	≤ 6 sdc _m
Nominal useful luminous flux 90°	200 lm
Rated useful luminous flux 90°	200 lm
Rated peak intensity	550 cd

Light technical data

Beam angle	30 °
Warm-up time (60 %)	< 1.00 s
Starting time	< 0.5 s
Nominal beam angle	30 °
Rated beam angle (half peak value)	30.00 °

Dimensions & weight



Overall length	39.0 mm
Diameter	34.7 mm
Outer bulb	MR35
Length	39.0 mm
Maximum diameter	35.0 mm

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000
Lumen main.fact.at end of nom.life time	0.70

Additional product data

Base (standard designation)	GU4
Lamp mercury content	0.0 mg
Mercury-free	Yes
Appropriate disposal acc. to WEEE	Yes
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value

Capabilities

Dimmable	No
-----------------	----

Certificates & standards


Product datasheet

Energy efficiency class	A+
Energy consumption	4 kWh/1000h

Country specific categorizations

ILCOS	DRR-7,3-12-GU4-34,7/30
Order reference	PMR112030 3.7W/

Light Distribution



Spectral power distribution



Guarantee

Equipment / Accessories

Product datasheet

Equipped with high-power LEDs

– Suitable for many commercially available electronic or conventional transformers

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899910423	PARATHOM MR11 20 30° 3.7 W/827 GU4	Shipping carton box 10	188 mm x 78 mm x 60 mm	0.88 dm ³	310.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For further products and actual information concerning LED lamps see

▶ www.osram.com/ledlamps

For Guarantee see

▶ www.osram.com/guarantee

Further information see

▶ www.osram.com/low-voltage-ledlamps

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.