

KEMET Part Number: C1812C333KCRACTU
(C1812C333KCRAC7800)

Capacitor, Ceramic, SMD, MLCC, High Voltage, Temperature Stable, 0.033 uF, +/-10% Tol, 500 V, X7R, 1812 (4532 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1812 (4532 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, High Voltage, Temperature Stable
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	4.5	+/-0.3
W	3.2	+/-0.3
T	1.4	+/-0.15
B	0.6	+/-0.35

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	1000

Specifications	
Capacitance:	0.033 uF
Voltage:	500 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Dissipation Factor:	2.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	3.03 GOhm
Dielectric Strength:	750 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours