

# Type: LXPRC-4W

### Phase Failure, Under and Over Voltage plus Time Delay


**TECHNICAL SPECIFICATION** 



- \*NEW\* 17.5mm DIN rail housing
- $\Box$ Microprocessor based
- True R.M.S. monitoring
- Monitors own supply and detects if one or more phases exceed the set Under or Over voltage trip levels
- $\Box$ Measures phase to neutral voltages
- Detects phase loss and neutral loss and operates irrespective of phase sequence
- Adjustments for Under and Over voltage trip levels
- Adjustment for Time delay (from an Under or Over voltage condition)
- 1 x SPDT relay output 8A
- Green LED indication for supply status
- Red LED indication for relay status

#### **FUNCTION DIAGRAM**

**Under and Over Voltage Monitoring** 



#### INSTALLATION AND SETTING

Installation work must be carried out by qualified personnel.

BEFORE INSTALLATION, ISOLATE THE SUPPLY.

Connect the unit as required. The Connection Diagram below shows a typical installation, whereby the supply to a load is being monitored by the Phase monitoring relay. If a fault should occur (i.e. fuse blowing), the relay will de-energise and assuming control of the external Contactor, de-energise the Contactor as well

#### Applying power.

- Set the "Over %" 3 adjustment to maximum and the "Under %" 5 adjustment to minimum. Set the "Delay (t)" 4 to minimum.
- Apply power and the green "Power supply" 1 and red "Relay" 2 LED's will illuminate, the relay will energise and contacts 15 and 18 will close. Refer to the troubleshooting table if the unit fails to operate correctly

#### Setting the unit (with power applied).

- Set the "Over %" and the "Under %" adjustments to give the required monitoring range.
- If large supply variations are anticipated, the adjustments should be set further from the nominal
- Set the "Delay (t)" adjustment as required. (Note that the delay is only effective should the supply increase above or drop below the set trip levels. However, if during an under voltage condition the supply drops below the 2<sup>nd</sup> under voltage trip level, any set time delay is automatically cancelled and the relay de-energises).

Note: If the supply voltage increases above the maximum "Over %" trip setting by approx. 5% or more, the relay will de-energise immediately.

#### Troubleshooting.

The table below shows the status of the unit during a fault condition.

Supply fault	Green LED	Red LED	Relay
Phase or neutral missing	On	Off	De-energised
Under or Over Voltage condition (during timing)	On	Flashing	Energised for set delay (t)
Under or Over Voltage condition (after timing)	On	Off	De-energised
Phase below 70% of Un (fixed under trip level [2])	On	Off	De-energised

#### Supply/monitoring voltage Un\* (L1, L2, L3, N): 120, 127, 220, 230, 240V AC (see note) 48 – 63Hz Frequency range: Supply variation: 70 – 130% Un Overvoltage category: III (IEC 60664) Rated impulse withstand voltage 4kV (1.2/50μS) IEC 60664 Power consumption (max.): 6VA Monitoring mode: Under and Over voltage Trip levels Under [2]: 70% of Un (fixed) ± 2% Under 75 - 95% of Un Over 105 - 125% of Un Measuring ranges Under [2] Under Over 120V: 84V 90 - 114V 126 - 150V 127V 89V 95 - 121V 133 - 159V 220V: 154V 165 - 209V 231 - 275V 173 – 218V 240V: 168V 180 - 228V 252 - 300V Hysteresis: ≈ 2% of trip level (factory set) Setting accuracy: Repeat accuracy: + 0.5% at constant conditions Immunity from micro power cuts: <50mS Response time ≈ 50mS Time delay (t): 0.2 – 10 sec. (± 5%) Note: actual delay (t) = adjustable delay + response time Delay from Phase/Neutral loss (tr): ≈ 150mS (worst case = tr x 2) Power on delay (Td): ≈ 1 sec. (worst case = Td x 2) Power on indication: Green LED Relay status indication Ambient temp: -20 to +60°C Relative humidity Output (15, 16, 18) SPDT relay 250V 8A (2000VA) Output rating: AC1 AC15 250V 5A (no), 3A (nc) DC1 25V 8A (200W) Electrical life: ≥ 150,000 ops at rated load 2kV AC (rms) IEC 60947-1 Dielectric voltage Rated impulse withstand voltage 4kV (1.2/50uS) IFC 60664 Orange flame retardant UL94 V0 Weight: 75g Mounting option: On to 35mm symmetric DIN rail to BS EN 60715 or direct surface mounting via 2 x M3.5 or 4BA screws


Approvals:

Terminal conductor size

The "Supply / monitoring voltage Un" refers to the phase to neutral nominal voltage for the product and voltage variants available. To convert these voltages to a phase to phase voltage, . multiply by 1.732.

80MHz - 2 7GHz) Emissions: EN 61000-6-4

#### **CONNECTION DIAGRAM**





## **SETTING DETAILS**

(Green) LED 2. Relay output / Timing status (Red) LED 3. "Over %" trip level adjustment^ "Delay" adjustment 5. Under %" trip level adjustment<sup>a</sup>

Ascaled as % of the nominal voltage "Un

1. Power supply status





using the black clips provided on the rear of the unit.

EMC: Immunity: EN 61000-6-2 (EN 61000-4-3 15V/m

Conforms to IEC. CE, Cand RoHS Compliant.

≤ 2 x 2.5mm<sup>2</sup> solid or stranded

