

**KEMET Part Number: C1206C470JBGACTU**  
(C1206C470JBGAC7800)

Capacitor, Ceramic, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 47 pF, +/-5% Tol, 630 V, C0G, 1206 (3216 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1206 (3216 metric)
Temperature Coefficient:	C0G
Part Type Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	1.6	+/-0.2
T	1	+/-0.10
B	0.5	+/-0.25

Specifications	
Capacitance:	47 pF
Voltage:	630 V
Tolerance:	+/-5%
Temperature Range:	-55/+125C
Dissipation Factor:	0.1%
Failure Rate:	N/A
Aging Rate:	0% loss/decade hour
Insulation Resistance:	100 GOhm
Dielectric Strength:	945 V

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	2500