


76-365

Designation : Wall lead holder.

Applications : putting away, sorting, stocking of banana leads, BNC leads, oscilloscope probes, ... on a wall or a panel. They do not lie on tables any more.



How to implement :

Three concrete $\text{Ø}6$ mm x 30 mm dowels and their three 34 mm-long screws are provided.



Step 1 of 3. I choose the wall or the panel the rack will be attached to. If the concrete dowels and their screws provided does not comply then I gather the right screws and dowels if necessary (I may not need any dowel). I gather a tool to tighten the screws (screwdriver Pozidriv 2 for the screws provided).

Step 2 of 3. I drill three holes into the wall or panel, this shall comply with the dowels or only the screws if I do not need the dowels. I insert the three dowels into the three holes if I need the dowels.

Step 3 of 3. I hold the rack in front of the three holes, I insert the three screws into the holes or dowels through the rack. With the tightening tool I screw and tighten the three screws.

The lead holder is ready to use.

1.5 mm-thick sheet steel to comply with heavy duty.

The nine 4.1 mm spacings can support usual 4 mm banana leads.


The two 5.8 mm spacings can support bigger leads like RG58 leads.


The two 2.8 mm spacings can support thinner leads like oscilloscope probes or 2 mm banana leads.

76-365



Designation : Wall lead holder.

Operating temperature range	-20 °C mini., +80 °C maxi..
Conformity	<ul style="list-style-type: none"> • European Directive "RoHS" 2011/65/EU. • European REACH regulation n°1907 / 2006.
Environment	<ul style="list-style-type: none"> • "RoHS" compliant, Pb ≤ 4 % in conductor, Pb ≤ 0.1 % in insulator, Hg ≤ 0.1 %, Cr VI ≤ 0.1 %, Cd ≤ 0.01 %, PBB ≤ 0.1 %, and PBDE ≤ 0.1 %. • REACH compliant, no substances from the candidate list of SVHC for authorisation at mass concentrations greater than 0.1 %
Materials	Painted steel.
Weight	0.215 kg.
Origin	 Designed and manufactured in France.
Reliability benchmark	Year of 1st placing on the market 1996.
Packaging	Set of 1 rack + 3 plastic dowels + 3 screws.



GLOSSARY :

ACCESSIBLE. Able to be touched with a standard test finger or test pin.

BASIC INSULATION. Insulation of HAZARDOUS LIVE parts which provides basic protection.

CAT II. Measurement or overvoltage category II. For measurement performed on / equipment connected to the building wiring.

CAT III. Measurement or overvoltage category III. For measurement performed on / equipment connected to part of a building wiring installation.

CAT IV. Measurement or overvoltage category IV. For measurement performed on / equipment connected to the origin of the electrical supply to a building.

CLEARANCE. Shortest distance in air between two conductive parts.

CREEPAGE DISTANCE. Shortest distance along the surface of a solid insulating material between two conductive parts.

CTI. Comparative Tracking Index of the insulating material in accordance with IEC 60112.

DOUBLE INSULATION. Insulation comprising both BASIC INSULATION and SUPPLEMENTARY INSULATION.

EN / IEC 60529. European / international standard regarding the degrees of protection provided by enclosures.

EN / IEC 61010-1. European / international standard regarding the safety requirements for electrical equipment for measurement, control, and laboratory use – Part 1: General requirements.

EN / IEC 61010-031:2008. European / international standard regarding the safety requirements for electrical equipment for measurement, control and laboratory use – Part 031: Safety requirements for hand-held probe assemblies for electrical measurement and test.

"LVD". European Directive 2014/35/EU on the harmonization of the laws of Member States relating to electrical equipment designed for use within certain voltage limits. (Usually called the Low Voltage Directive.)

MAINS. Low-voltage electricity supply system to which the equipment concerned is designed to be connected for the purpose of powering the equipment.

MAINS CIRCUIT. Circuit which is intended to be directly connected to the MAINS for the purpose of powering the equipment.

OVERVOLTAGE CATEGORY. Numeral defining a TRANSIENT OVERVOLTAGE condition.

POLLUTION. Addition of foreign matter, solid, liquid or gaseous (ionized gases), that may produce a reduction of dielectric strength or surface resistivity.

POLLUTION DEGREE. Numeral indicating the level of POLLUTION that may be present in the environment.

POLLUTION DEGREE 1. No POLLUTION or only dry, non-conductive POLLUTION occurs, which has no influence.

POLLUTION DEGREE 2. Only non-conductive POLLUTION occurs except that occasionally a temporary conductivity caused by condensation is expected.

REINFORCED INSULATION. Insulation which provides protection against electric shock not less than that provided by DOUBLE INSULATION.

"RoHS". European Directive 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

SOLID INSULATION. Insulating materials.

SUPPLEMENTARY INSULATION. Independent insulation applied in addition to BASIC INSULATION in order to provide protection against electric shock in the event of a failure of BASIC INSULATION.

TRANSIENT OVERVOLTAGE. Short duration overvoltage of a few milliseconds or less, oscillatory or non-oscillatory, usually highly damped.

WORKING VOLTAGE. Highest r.m.s. value of the a.c. or d.c. voltage across any particular insulation which can occur when the equipment is supplied at rated voltage.