



Analog Devices Welcomes Hittite Microwave Corporation

NO CONTENT ON THE ATTACHED DOCUMENT HAS CHANGED



www.hittite.com

www.analog.com

HMC767* Product Page Quick Links

Last Content Update: 11/01/2016

Comparable Parts

View a parametric search of comparable parts

Evaluation Kits

• HMC767LP6CE Evaluation Board

Documentation 🖵

Data Sheet

• HMC767 Data Sheet

User Guides

• PLLs with Integrated VCO - Microwave Applications Product & Operating Guide

Reference Materials

Quality Documentation

- HMC Legacy PCN: LP6CE and LP6GE QFN Alternate assembly source
- Package/Assembly Qualification Test Report: LP6, LP6C, LP6G (QTR: 2014-00368)

Technical Articles

 Low Cost PLL with Integrated VCO Enables Compact LO Solutions

Design Resources 🖵

- HMC767 Material Declaration
- PCN-PDN Information
- Quality And Reliability
- Symbols and Footprints

Discussions 🖵

View all HMC767 EngineerZone Discussions

Sample and Buy

Visit the product page to see pricing options

Technical Support

Submit a technical question or find your regional support number

^{*} This page was dynamically generated by Analog Devices, Inc. and inserted into this data sheet. Note: Dynamic changes to the content on this page does not constitute a change to the revision number of the product data sheet. This content may be frequently modified.

THIS PAGE INTENTIONALLY LEFT BLANK





FRACTIONAL-N PLL WITH INTEGRATED VCO, 8.45 - 9.55 GHz

Features

- RF Bandwidth: 8.45 GHz to 9.55 GHz
- Fractional or Integer Modes
- Ultra Low Phase Noise
 9.0 GHz; 50 MHz Ref.
 -107 / -102 dBc/Hz @ 10 kHz (Int / frac)
 -138 dBc/Hz @ 1 MHz (Open Loop)
- Figure of Merit (FOM) -230 / -227 dBc/Hz (int / Frac)

Typical Applications


• VSAT Radio

PLL WITH INTEGRATED VCO - SMT

- Microwave Point-To-Point Radios
- Test Equipment & Industrial Control

Functional Diagram

- 24-bit Step Size, Resolution 3 Hz typ
- 350 MHz, 14-bit reference path input
- Frequency And Phase Modulation
- Integrated Frequency Sweeper
- Triggered Frequency Hopping
- External Triggering
- 40 Lead 6 x 6 mm SMT Package: 36 mm²
- Military End-Use
- Phased Array Applications
- FMCW Radar Systems



[1] Please refer to the pin description table for details

For price, delivery and to place orders: Hittite Microwave Corporation, 2 Elizabeth Drive, Chelmsford, MA 01824 Phone: 978-250-3343 Fax: 978-250-3373 Order On-line at www.hittite.com Application Support: Phone: 978-250-3343 or apps@hittite.com

1



FRACTIONAL-N PLL WITH INTEGRATED VCO, 8.45 - 9.55 GHz

General Description

The HMC767LP6CE is a fully functioned Fractional-N Phase-Locked-Loop (PLL) Frequency Synthesizer with an integrated Voltage Controlled Oscillator (VCO). The input reference frequency range is DC to 350 MHz while the advanced delta-sigma modulator design in the fractional synthesizer allows both ultra-fine step sizes and very low spurious products. The highly integrated structure provides excellent phase noise performance over temperature, shock and process. In addition, the HMC767LP6CE offers frequency sweep and modulation features, external triggering, double-buffering, exact frequency control, phase modulation and more. The HMC767LP6CE is packaged in a leadless QFN 6 x 6 mm surface mount package.

For theory of operation and register map refer to the "PLLs w/ Integrated VCO - Microwave VCOs" Operating Guide. To view the <u>Operating Guide</u>, please visit www.hittite.com and choose HMC767LP6CE from the "Search by Part Number" pull down menu.

Parameter	Condition	Min.	Тур.	Max.	Units
RF Output Characteristics					
VCO Output Frequency Range		8.45	9.0	9.55	GHz
VCO Output Power ^[1]			12		dBm
VCO Tuning Voltage		2		13	V
VCO Tuning Sensitivity	V _{TUNE} = 6V		150		MHz/V
Frequency Pulling	into a 2:1 VSWR		6		MHz pp
Frequency Pushing	V _{TUNE} = 5V		20		MHz/V
Frequency Drift Rate			0.8		MHz/ °C
Sub Harmonic (1/2)			40		dBc
Harmonic (2 nd)			15		dBc
Harmonic (3 rd)			40		dBc
VCO SSB Phase Noise @ 100 kHz Offset (Open Loop)	V _{TUNE} = +5V Fvco = 9.0 GHz		-115		dBc/Hz
Synthesizer In-Band SSB Phase Noise @ 10 kHz Offset (Integer / Fractional)	Fref = 50 MHz Fvco = 9.0 GHz Loop BW = 100 kHz		-107/-102		dBc/Hz
Synthesizer Noise Floor, Figure Of Merit (Integer / Fractional)			-230 / -227		dBc/Hz
Synthesizer Fractional Spurs ^[2]			-65	-38	dBc
Synthesizer Frequency Settling Time (100 MHz Step)	9.0 GHz to 9.1 GHz Loop BW = 100 kHz, 10°		433		μs
RF/2 Divider Range	· · ·				
> 4GHz Integer Mode	16 bit, even values only	32		131,070	
< 4GHz Integer Mode	16 bit, all values	16		65,535	
> 4GHz Fractional Mode	16 bit	40		131,065	
< 4GHz Fractional Mode	16 bit	20		65,531	

Electrical Specifications, $T_A = +25^{\circ}$ C; VCCVCO, VDDLS, VPPCPA = +5V; RVDD, AVDD, VCCPS, VCCHF, VDDPD, DVDD, VDDIO = + 3.3V

[1] See power output vs. tuning voltage graph for power slope.

[2] Actual spur level is dependent on loop parameters and will increase at division ratios closest to integer boundaries.





FRACTIONAL-N PLL WITH INTEGRATED VCO, 8.45 - 9.55 GHz


Electrical Specifications (Continued)

Parameter	Condition	Min.	Тур.	Max.	Units
REF Input Characteristics			•		
Frequency Range (3.3V)		DC	50	350	MHz
Power From 50Ω Source	With off chip 100Ω termination		6		dBm
Return Loss		-16		-8	dBm
Ref Divider Range (14-Bit)		1		16,383	
Phase Detector Rate					
Integer Mode		DC	50	115	MHz
Fractional Mode A		DC	50	80	MHz
Fractional Mode B		DC	50	100	MHz
Charge Pump			<u> </u>		
CP Output Current	20µA steps CP_gain = CP_current ÷ 2∏ (amps/rad)	0.02		2.5	mA
СР НіК	see "Charge Pump Gain" section of "Operation Guide"		3.5	6	mA
Logic Inputs					
Switching Threshold (Vsw)	VIH/VIL within 50mV of Vsw	38	47	54	%VDDIO
Logic Outputs					•
VOH Output High Voltage			VDDIO		V
VOL Output Low Voltage			0		v
Output Impedance: Pull Up	VDDIO = 3.3V	115	150	180	Ω
Output Impedance: Pull Dn	VDDIO = 3.3V	130	135	210	Ω
DC Load				1.5	mA
Digital Output Driver Delay SCK to Digital Output Delay	1.7 ns with a 3 pF load		0.5ns + 0.2ns/pF 8.2ns + 0.2ns/pF		ns
Power Supply Voltages					
VCCVCO - VCO Supply		4.75	5.0	5.25	V
RVDD, AVDD, VCCPS, VCCHF, VDDPD - Analog Supply	all must be equal	2.7	3.3	3.5	v
DVDD, VDDIO - Digital Supply	both must be equal	2.7	3.3	3.5	V
VDDLS, VPPCPA - Charge pump	both must be equal	4.7	5.0	5.2	V
Power Supply Currents	· · · · · · ·				
5.0V - VCO Current Consumption		230	250	270	mA
3.3V - PLL Current Consumption	all modes	34	54	95	mA
5.0V - Charge Pump Current Consumption	all modes	3	7	16	mA
Power Down Current	except VCO	-		100	μA
Bias Reference Voltage (Pin 20)	Measured with 10 G Ω meter	1.88	1.92	1.96	v







SSB Phase Noise vs. Frequency, Integer Mode, Fref = 50 MHz, Loop BW = 100 kHz



SSB Phase Noise Fractional Spurs @ 9.01 GHz, Fref = 10 MHz, Loop BW = 10 kHz




Reference Input Sensitivity, Square Wave, 50Ω




FRACTIONAL-N PLL WITH INTEGRATED VCO, 8.45 - 9.55 GHz


SSB Phase Noise vs. Temperature @ 9.0 GHz, Integer Mode, Fref = 50 MHz, Loop BW = 100 kHz




SSB Phase Noise vs. Reference Freq. & Loop BW @ 9.0 GHz, Integer Mode





Reference Input Sensitivity, Sinusoid Wave, 50Ω

















Open Loop VCO SSB Phase Noise vs. Tuning Voltage





FRACTIONAL-N PLL WITH INTEGRATED VCO, 8.45 - 9.55 GHz



Output Power vs. Tuning Voltage, Vcc = +5V











FRACTIONAL-N PLL WITH INTEGRATED VCO, 8.45 - 9.55 GHz


Absolute Maximum Ratings

-
+5.5V
0 to +15V
-0.3V to +3.6V
-0.3V to +3.6V
-0.3V to +5.5V
1 KΩ min.
20 ns
-0.25V to VDDIO + 0.5V
-65° C to +125° C
Class 1A

Reliability Information

Junction Temperature To Maintain 1 Million Hours MTTF	135 °C
Nominal Junction Temperature (T = +85°C)	121.3 °C
Thermal Resistance (Junction to GND Paddle, 5V Supply)	24.8 °C/W
Operating Temperature	-40 to +85°C

Outline Drawing



REFER TO HITTITE APPLICATION NOTE FOR SUGGESTED PCB LAND PATTERN.

Package Information

Part Number	Package Body Material	Lead Finish	MSL Rating	Package Marking ^[1]
HMC767LP6CE	RoHS-compliant Low Stress Injection Molded Plastic	100% matte Sn	MSL3	<u>H767</u> XXXX
[1] 4-Digit lot number	XXXX			

PLL WITH INTEGRATED VCO - SM





FRACTIONAL-N PLL WITH INTEGRATED VCO, 8.45 - 9.55 GHz

Pin Descriptions

Pin Number	Function	Description	
1, 9 - 14, 22, 23, 26, 35	N/C	No connection. These pins may be connected to RF/DC ground. Performance will not be affected.	
2 - 5, 37, 39	GND ^[1]	Pins must be connected to RF/DC ground	
7	GND	This pin and package bottom must be connected to RF/DC ground	
6	VTUNE	Control voltage input. Modulation port bandwidth dependent on drive source impedance.	
8	VCCVCO2	+ 5V power supply for VCO.	
15	VCCHF	Analog power supply for RF buffer. Nominal + 3.3V, 6 mA max.	
16	VDDLS	Power supply for PFD to CP level shifters. Nominal + 5V, 5 mA max., Fpd dependent.	
17	VPPCPA	Power Supply for the charge pump. Nominal + 5V, 10 mA Max.	
18	CP	Charge pump output	
19	AVDD	Power Supply for analog bias generation. Nominal + 3.3V, 2 mA Max.	
20	BIAS ^[2]	External bypass decoupling for precision bias circuits, 1.920V ±2 mV is generated internally	
21	RVDD	Power Supply for Reference Path. Nominal + 3.3V, 15 mA Max., reference dependent	
24	XREFP	Reference input. DC bias is generated internally. Normally AC coupled externally.	
25	VDDPD	Power supply for phase detector. Nominal + 3.3V. Decoupling for this supply is critical. 5 mA max., Fpd dependent.	
27	CEN	CMOS input, hardware chip enable.	
28	SEN	CMOS input, serial port latch enable.	
29	SCK	CMOS input, serial port clock.	
30	SDI	CMOS input, serial port data.	
31	DVDD	Power supply for digital. Nominal + 3.3V, 25 mA max., Fpd dependent.	
32	VDDIO	Power supply for digital I/O. Nominal + 3.3V, 8 mA max. (only when driving LD_SDO)	
33	LD_SDO	CMOS output. General purpose output; lock detect, serial data out, others, selectable	
34	VCCPS	Power supply for RF divider. Nominal + 3.3V, 35 mA max.	
36	TRIG	CMOS input. External trigger.	
38	RFOUT	RF output (AC coupled).	
40	VCCVCO1	Power Supply for VCO. Nomimal +5V, High Current, VCO dependent	

[1] Pin is not connected internally, however, pin must be connected to GND to maintain product family pin for pin compatibility.


[2] BIAS ref voltage (pin 20) cannot drive an external load, and must be measured with a 10 GOhm meter such as Agilent 34410A; a typical 10 Mohm DVM will read erroneously.



FRACTIONAL-N PLL WITH INTEGRATED VCO, 8.45 - 9.55 GHz



Evaluation PCB



The circuit board used in the application should use RF circuit design techniques. Signal lines should have 50 Ohm impedance while the package ground leads and exposed paddle should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Hittite upon request.

Evaluation PCB Schematic

To view this Evaluation PCB Schematic please visit www.hittite.com and choose HMC767LP6CE from the "Search by Part Number" pull down menu to view the product splash page.

Evaluation Order Information

Item	Contents	Part Number
Evaluation PCB Only	HMC767LP6CE Evaluation PCB	130369-HMC767LP6CE
Evaluation Kit	HMC767LP6CE Evaluation PCB USB Interface Board 6' USB A Male to USB B Female Cable CD ROM (Contains User Manual, Evaluation Software, Hittite PLL Design Software)	EKIT01-HMC767LP6CE

PLL WITH INTEGRATED VCO - SMT