






- \*NEW\* 17.5mm DIN rail housing
- □ Instantaneous Contact (Relay 1)
  - Delay On Operate timing function (Relay 2)
- 7 Selectable time ranges (0.1 seconds 100 hours)
- Fine adjustment of selected time range
- Multi-voltage input (12 230V AC/DC)
- 2 x SPDT relay output 8A
- Green LED indication for supply / timing status
- Red LED indication for relay statuses
  - Conforms to IEC 61812

# FUNCTION DIAGRAMS



# • <u>INSTALLATION AND SETTING</u>

- BEFORE INSTALLATION, ISOLATE THE SUPPLY.
- Connect the unit as required.

#### Setting the unit

• Set the "Range" 
② to the required position (depending on whether seconds, minutes or hours are required), then set the "Set %" adjustment ⑤ as required. The "Set %" is a % of the selected range, so 60% of the 1 − 10 hour range will give 6 hours.

#### Applying power

- Apply power and the green LED will start flashing to indicate timing is in progress. Contacts 15 and 18 will close as soon as power is applied (Instantaneous Relay RLY1) and the red relay LED
   will illuminate. Contacts 25 and 26 (Timed Relay RLY2) will remain closed during this period
- At the end of the delay period "t" contacts 25 and 26 will open 25 and 28 will close. The red relay LED @ will illuminate.
- Both relays will remain in the energised state until power is removed. Re-applying power will
  repeat the whole process again.


### Note:

<sup>1</sup> In accordance with IEC 61812, the green LED is permitted to extinguish during a voltage dip or momentary interruption of the power supply providing the state of the output relay does not change.

<sup>2</sup> The dip / interruption (reset) duration and levels are defined in the product standard however, the standard allows for these to be different from the levels actually specified.

#### **TECHNICAL SPECIFICATION** Supply voltage U (A1, A2): 12 - 230V AC/DC 48 - 63Hz (AC supplies) AC: +15/-10% DC: +/-15% Frequency range Supply variation: Overvoltage category: III (IEC 60664) Rated impulse withstand voltage 4kV (1.2/50µS) IEC 60664 Power consumption (max.): 2.6VA 0.94W 6.8VA 1.9W 0.6VA 0.8VA 0.52W 0.48W Timing function (RLY1): Instantaneous Contact Time delay: Timing function (RLY2): <100mS (to relay energising) Delay On Operate Timing ranges (7): Seconds: Minutes Hours: 0.1 - 10.1 - 10.1 - 11-10 1-10 10 - 100 Reset time<sup>2</sup>: <100mS Accuracy: ± 1% of maximum full scale Adjustment accuracy: < 5% of maximum full scale ± 0.5% at constant conditions (IEC 61812) Repeat accuracy: Drift with temperature: $\pm\,0.05\%$ / °C Drift with voltage +0.2%/V Green LED Power on indication / Timing<sup>1</sup>: Relay status (Instantaneous - RLY1) Relay status (Delay On Op. - RLY2) Red LFD Red LED -20 to +60°C Ambient temp: Relative humidity: +95% Output (15, 16, 18 / 25, 26, 28): SPDT relay (x2) 250V 8A (2000VA) Output rating: AC1 AC15 250V 5A (no), 3A (nc) DC1 25V 8A (200W) Electrical life: ≥ 150,000 ops at rated load Dielectric voltage 2kV AC (rms) IEC 60947-1 4kV (1.2/50μS) IEC 60664 Rated impulse withstand voltage: Housing Orange flame retardant UL94 Weight: ≈ 80g Mounting option: On to 35mm symmetric DIN rail to BS EN 60715 or direct surface mounting via 2 x M3.5 or 4BA screws using the black clips provided on the rear of the unit. Terminal conductor size ≤ 2 x 2.5mm² solid or stranded Approvals Conforms to IEC 61812. CE, C-tick Cand RoHS Compliant. EMC: Immunity: EN 61000-6-2 (EN 61000-4-3 10V/m 80MHz - 2.7GHz)

#### • CONNECTION DIAGRAM




# SETTING DETAILS


Installation work must be carried

out by qualified personnel.

1. Power supply status / Timing (Green) LED 2. Relay 2 output status (Red) LED 3. Relay 1 output status (Red) LED 4. Time delay "Range" selector

5. "Set %" adjustment





Emissions: EN 61000-6-4

