

Type: LXPRC/S-4W


Phase Failure, Phase Sequence, Under and Over Voltage plus Time Delay



- *NEW* 17.5mm DIN rail housing
- Microprocessor based
- True R.M.S. monitoring
- Monitors own supply and detects if one or more phases exceed the set Under or Over voltage trip levels
- Measures phase to neutral voltages
- Detects incorrect phase sequence, phase loss and neutral loss
- Adjustments for Under and Over voltage trip levels
- Adjustment for Time delay (from an Under or Over voltage condition)
- 1 x SPDT relay output 8A
- Green LED indication for supply status
- Red LED indication for relay status

FUNCTION DIAGRAM

Under and Over Voltage Monitoring



INSTALLATION AND SETTING

BEFORE INSTALLATION, ISOLATE THE SUPPLY.

Installation work must be carried out by qualified personnel.

Connect the unit as required. The Connection Diagram below shows a typical installation, whereby the
supply to a load is being monitored by the Phase monitoring relay. If a fault should occur (i.e. fuse
blowing), the relay will de-energise and assuming control of the external Contactor, de-energise the
Contactor as well.

Applying power.

- Set the "Over " adjustment to maximum and the "Under " adjustment to minimum. Set the "Delay (t)" to minimum.
- Apply power and the green "Power supply" 1 and red "Relay" 2 LED's will illuminate, the relay will
 energise and contacts 15 and 18 will close. Refer to the troubleshooting table if the unit fails to operate
 correctly.

Setting the unit (with power applied).

- Set the "Over %" and the "Under %" adjustments to give the required monitoring range.
- If large supply variations are anticipated, the adjustments should be set further from the nominal voltage.
- Set the "Delay (t)" adjustment as required. (Note that the delay is only effective should the supply
 increase above or drop below the set trip levels. However, if during an under voltage condition the
 supply drops below the 2nd under voltage trip level, any set time delay is automatically cancelled and the
 relay de-energises).

Note: If the supply voltage increases above the maximum "Over%" trip setting by approx. 5% or more, the relay will de-energise immediately.

Troubleshooting.

The table below shows the status of the unit during a fault condition.

Supply fault	Green LED	Red LED	Relay
Phase or neutral missing	On	Off	De-energised
Phases reversed (no delay)	Flashing	Off	De-energised
Under or Over Voltage condition (during timing)	On	Flashing	Energised for set delay (t)
Under or Over Voltage condition (after timing)	On	Off	De-energised
Phase below 70% of Un (fixed under trip level [2])	On	Off	De-energised

TECHNICAL SPECIFICATION Supply/monitoring voltage

Un* (L1, L2, L3, N):

	Frequency range: Supply variation: Overvoltage category: Rated impulse withstand v Power consumption (max.	-	48 – 63Hz 70 – 130% Un III (IEC 60664) 4kV (1.2/50µS) IEC 60664 6VA		* Please state Supply/monitoring voltage when ordering	
ш	Monitoring mode: Trip levels:		Under and Over	rvoitage		
	•	Inder [2]: Under: Over:	70% of Un (fixed) ± 2% 75 – 95% of Un 105 – 125% of Un			
	Measuring ranges:		Under [2]	Under	Over	
Ш		120V:	84V	90 – 114V	126 – 150V	
Ш.		127V:	89V	95 – 121V	133 – 159V	
Ш		220V:	154V	165 – 209\	/ 231 – 275V	
Ш.		230V:	161V	173 – 218\	/ 241 – 288V	
Ш		240V:	168V	180 – 228\	/ 252 – 300V	
	Hysteresis:		≈ 2% of trip level (factory set)			
111	Setting accuracy:		± 3%			
	Repeat accuracy:		± 0.5% at constant conditions			
Ш	Immunity from micro power cuts:		<50mS			
_	Response time:		≈ 50mS			
Ш	Time delay (t):	0.2 – 10 sec. (± 5%)				
Ш			Note: actual delay (t) = adjustable delay + response time			

120, 127, 220, 230, 240V AC (see note)

Note: actual delay (t) = adjustable delay + response time
≈ 150mS (worst case = tr x 2)

Power on delay (Td):

≈ 15ec. (worst case = Td x 2)

Power on indication:

Green LED

 Ambient temp:
 -20 to +60°C

 Relative humidity:
 +95% max.

 Output (15, 16, 18):
 SPDT relay

 Output rating:
 AC1
 250V 8A (2000VA)

 AC15
 250V 5A (no), 3A (nc)

 DC1
 25V 8A (2000V)

≥ 150,000 ops at rated load

Red LED

Dielectric voltage: 2kV AC (rms) IEC 60947-1
Rated impulse withstand voltage: 4kV (1.2/50µS) IEC 60664
Housing: Orange flame retardant UL94

Meight: 75g

Mounting option: On to 35mm symmetric DIN rail to BS EN 60715

or direct surface mounting via 2 x M3.5 or 4BA screws
using the black clips provided on the rear of the unit.

Terminal conductor size ≤ 2 x 2.5mm² solid or stranded

Approvals: Conforms to IEC. CE, Cand RoHS Compliant.


EMC: Immunity: EN 61000-6-2 (EN 61000-4-3 15V/m 80MHz - 2.7GHz) Emissions: EN 61000-6-4

Relay status indication:


Electrical life:


The "Supply / monitoring voltage Un" refers to the phase to neutral nominal voltage for the product and voltage variants available. To convert these voltages to a phase to phase voltage, multiply by 1.732.

CONNECTION DIAGRAM



SETTING DETAILS







Broyce Control Ltd., Pool Street, Wolverhampton, West Midlands WV2 4HN. England