

12VDC 3.5A Power Supply



Description:

This 12VDC 3.5A power supply has a 90-264vac input & a standard 2 pin Fig.8 input connector. It carries international safety approvals and meets latest energy efficiency requirement. Featuring high reliability with a M.T.B.F of 50K hours at 25 degrees C, the units provides a single voltage regulated output at 42W max, & is fitted with a 2.1 x 5.5 x 12mm conn. Polarity + ve centre

General Spec



Part Numbers	SW4500A	Leakage Current	shall not exceed mA
Output	12vdc regulated (3.5A max)	Input Current (RMS Max.)	max
Current Min.	0.01A	Hi-Pot Spec	3000Vac 10mA 1 min. (I.P. to O.P.)
Power (watts)	42W Max	No load power consumption	Max
Line Reg	+/-5% at rated load	Operating Temperature	0 to 40 degrees C
Total Output Regulation	+/-5% at 0—100% load	Storage Temperature	-20 to 80 degrees C
Ripple & Noise (mV p-p)	120mV P-P	Operating Humidity	10% to 90%
Protections	Over Current and Short Circuit	Safety Approvals	CE, TUV, C-Tick, cUL, PSE
Case Size	126.4 x 52 x 35.5mm	EMC Standards	EN55022:2006+A1:2007 / EN6100-3-2 / EN6100-3-3
Weight (approx.)	224g	Pb-free	Yes RoHS Compliant
DC Cord	1.5 Metres	MTBF	50K Hours at 25 degrees C
DC Plug	2.1 x 5.5 x 12mm +ve centre		
Rated Input Voltage	100-240Vac		
Full Input Voltage Range	90-264Vac		
Rated Frequency	50-60Hz		
Full Frequency Range	47-63Hz		
Efficiency	VI		

Full specification documents on each part included in this data sheet are available on request from PowerPax UK Ltd. PowerPax accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice