



Terminal Protection to IP20

43880 W. 17.5r



Compact 17.5mm DIN rail housing

Microprocessor based

True R.M.S. monitoring
 Selectable nominal voltages to suit most popular single phase supply voltages

☐ Monitors own supply and detects if the set Under or Over voltage trip levels are exceeded

Adjustments for Under and Over voltage trip levels

Adjustment for Time delay

Independent relay outputs - Under voltage monitoring (RLY2) / Over voltage monitoring (RLY1)


2 x SPDT relay output 5A

□ Green LED indication for supply status

Individual Red LED indication for both relay statuses

#### FUNCTION DIAGRAM

**Under and Over Voltage Monitoring** 



### INSTALLATION AND SETTING

Installation work must be carried out by qualified personnel.

 BEFORE INSTALLATION, ISOLATE THE SUPPLY.
 Connect the unit as required. The Connection Diagram below shows a typical installation, whereby the supply to a load is being monitored by the Voltage monitoring relay. If a fault should occur (i.e. fuse blowing), the relay will de-energise and assuming control of the external Contactor, de-energise the Contactor as well.

#### Applying power.

- Set the "Nominal (Un)" voltage selector to match that of the voltage being monitored.
- Set the Over " adjustment to maximum and the "Under " adjustment to minimum. Set the "Delay (t)"
   It a minimum
- Apply power and the green "Power supply" 1 LED will illuminate. Both the red "RLY1" 2/"RLY2" 8 LED's will illuminate and corresponding RLY1 and RLY2 relays energise after the short Power on delay (Td).
- Refer to the Troubleshooting table if the unit fails to operate correctly

## Setting the unit (with power applied).

- Set the "Over %" and the "Under %" adjustments to give the required monitoring range.
- If large supply variations are anticipated, the adjustments should be set further from the nominal voltage.
- Set the "Delay (t)" adjustment as required. (Note that the delay is only effective should the supply increase
  above or drop below the set trip levels. However, if during an under voltage condition the supply drops below
  the 2<sup>nd</sup> under voltage trip level, any set time delay is automatically cancelled and both relays de-energise
  immediately).


## Troubleshooting.


The table below shows the status of the unit during a particular fault condition.


| Supply fault                            | Green LED | Red LED  | Red LED  | Relay RLY1       | Relay RLY2       |
|---|-----------|----------|----------|------------------|------------------|
| Under voltage condition (during timing) | On        | On       | Flashing | Energised        | En for delay (t) |
| Under voltage condition (after timing)  | On        | Off      | Off      | Energised        | De-energised     |
| Over voltage condition (during timing)  | On        | Flashing | On       | En for delay (t) | Energised        |
| Over voltage condition (after timing)   | On        | Off      | On       | De-energised     | Energised        |
| Supply < fixed under trip level [2]     | On        | Off      | Off      | De-energised     | De-energised     |

#### **TECHNICAL SPECIFICATION** Supply/monitoring voltage Un (A1, A2): LCVR/2 (LV)\* 110, 115V AC LCVR/2 (HV)\* 220, 230, 240V AC Frequency range: 48 – 63Hz Supply variation: Overvoltage category: LV: 70 - 150V HV: 140 - 315V AC III (IEC 60664 4kV (1.2/50µS) IEC 60664 Rated impulse withstand voltage Power consumption (max.) Monitoring mode: Under and Over voltage Trip levels Under [2]: Fixed ± 2% see below Under 75 - 95% of Un 105 – 125% of Ur Measuring ranges Nominal (Un) Under [2] Under Over LCVR/2 (LV) 110V 83 – 105V 116 - 138V 74V 156 – 198V 218 – 260V 115V LCVR/2 (HV) 220V 140V 165 - 209V 231 - 275V 230V 240V 252 - 300V 153V 180 - 228V Hysteresis: ≈ 2% of trip level (factory set) Setting accuracy: ± 3% Repeat accuracy $\pm$ 0.5% at constant conditions <50ms Immunity from micro power cuts Response time ≈ 50ms Time delay (t): 0.2 – 10s (± 5%) Note: actual delay (t) = adjustable delay + response time Power on delay (Td): ≈ 1s (worst case = $Td \times 2$ ) Reset time: Power on indication: Green LFD Relay status indication Red LED x2 Ambient temperature: -20 to +60°C Relative humidity +95% max 2 x SPDT relay Output (15, 16, 18 / 25, 26, 28) Output rating AC1 250V 5A (1250VA) AC15 250V 2A 25V 5A (125W) DC1 Electrical life: ≥ 150,000 ops at rated load Dielectric voltage: 2kV AC (rms) IEC 60947-1 Rated impulse withstand voltage 4kV (1.2/50μS) IEC 60664 Housing: Orange flame retardant UL94 Weight 90g On to 35mm symmetric DIN rail to BS EN 60715 or direct Mounting option: surface mounting via 2 x M3.5 or 4BA screws using the black clips provided on the rear of the unit. Approvals: Conforms to IEC. CE, Cand RoHS Compliant. Immunity: EN 61000-6-2 Emissions: EN 61000-6-4

# • CONNECTION DIAGRAM









Broyce Control Ltd., Pool Street, Wolverhampton, West Midlands WV2 4HN. England