## Product data sheet Characteristics

# VZ7

# TeSys VARIO - auxiliary contact block - 1 NC early-break+1 NO late-make

Product availability: Stock - Normally stocked in distribution facility

Price\*: 42.80 USD



#### Main

IVIAIII		
Range	TeSys	-
Device short name	VZ	9
Product or component type	Auxiliary contact block	<del>-</del>
Performance level	High performance	landiahilik Anton
Contacts type and composition	1 NO + 1 NC	<u> </u>
Contact operation	Late-make 1 NO Early-break 1 NC	## ###################################
Product compatibility	V02 V1 V2 V3 V4 V5 V6 V0	is not to be used for determining
Network type	AC DC	for and
Network frequency	50/60 Hz	

## Ordering and shipping details

Category	21730 - V VARIO SWITCH	nten
Discount Schedule	CP1	Ď
GTIN	00785901305743	<u></u>
Nbr. of units in pkg.	1	
Package weight(Lbs)	0.12	E
Returnability	Υ	
Country of origin	CZ	
		· <u></u>

#### Contractual warranty

Warranty period	18 months	
-----------------	-----------	--

## Complementary

Mounting location	Right
System Voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[lth] conventional free air thermal current	12 A
[Ithe] conventional enclosed thermal current	10 A
Mechanical durability	100000 cycles
Electrical durability	30000 cycles DC-11 100000 cycles AC-15
Connections - terminals	Screw clamp terminals 2 cable 00 in² (12.5 mm²) - cable stiffness: solid Screw clamp terminals 2 cable 00 in² (0.751.5 mm²) - cable stiffness: flexible - with cable end
Tightening torque	6.19 lbf.in (0.7 N.m) - on screw clamp terminals
Height	2.56 in (65 mm)
Width	0.79 in (20 mm)
Depth	1.91 in (48.5 mm)
Product weight	0.11 lb(US) (0.05 kg)

#### Environment

Standards	IEC 60947-5
Product certifications	CSA GL UL
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-4122 °F (-2050 °C)
Fire resistance	1760 °F (960 °C) conforming to IEC 60695-2-1