

Identification

Type Designation	LR3 48-5/630	Type of reactor	3~ Line Reactor
Series	LR3	Core Rating	26308.80 var
Core type	3UI 210/63	Drive HP	450



Technical Data

No. of phase		3
Circuit type		III0
Rated Voltage	[V]	480
Rated current	[A]	630.0
Rated Frequency	[Hz]	50 - 60
Impedance	[%]	5.0
Inductance L	[mH]	0.059
L tolerance	[%]	±10%
Linearity		150% In
Losses (typical)	[W]	256.30
Test voltage	[kV]	4.0
Isolation System Class		class 180

Operating conditions

Ambient temperature	[°C]	-10 ... +40°C
Ambient temperature	[F]	14 ... 104°F
Type of cooling		AN
Operating conditions		24/7

Standards


Type:	Signs
VDE 0570 / EN 61 558 Part 1 VDE 0570 / EN 61 558 Part 20	 

Approvals

UL 508	 E219022 NMTR
UL 5085-1	 E103521 XPTQ

Variations may apply due to material's and production's tolerances. Objected to modifications without notice.

Dimensions / Mounting in Inches



A	B	C*	F	D	d1	d2	E	e1	e2	Drill
18.90	8.07	14.65	-	12.44	14.57	17.70	5.47	5.79	5.10	0.47
										0.47
										0.47

* = Typical variable air gab

Weight

Weight	[kg]	89.84
	[lbs]	198.06

Notes

Technical specifications in the drawing are not binding. General tolerance to DIN 7168-m. Subject to change.
Mounting plates also available in stainless steel as OEM application. Ask for details.