

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0039000079**  
**Status:** **Active**  
**Overview:** Mini-Fit Jr.™ Power Connectors  
**Description:** Mini-Fit® Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 16 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification TS-5556-002-001 (PDF)</a>
<a href="#">Product Specification PS-5556-001 (PDF)</a>	<a href="#">Packaging Specification PK-5556-001-002 (PDF)</a>
<a href="#">Product Specification PS-5556-002-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<u>5556</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Mini-Fit Jr.™ Power Connectors</u>
Packaging Alternative	<u>39-00-0080 (Loose)</u>
Product Name	Mini-Fit®
UPC	800753749986

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	130.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm²	N/A

**Electrical**


Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	5556PBT3
--------------------	----------

**Reference - Drawing Numbers**

Packaging Specification	PK-5556-001-002
Product Specification	PS-5556-001, PS-5556-002-001, TS-5556-002-001
Sales Drawing	SD-5556****



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

5556 Series

**Mates With**

5558 Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, 5566 , 5569

**Use With**

5557 Mini-Fit Jr.™ Receptacle Housing, 30067 Mini-Fit® TPA, 42474 Mini-Fit® BMI Panel Mount, 5559 Mini-Fit Jr.™ Plug Housing, Dual Row

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

<b>Description</b>	<b>Product #</b>
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<u>0638190900</u>
Extraction Tool	<u>0011030044</u>
FineAdjust™	<u>0639039400</u>
Applicator for Insulation OD 2.20-2.45mm, Optimized for 16 AWG Only	
FineAdjust™	<u>0639041400</u>
Applicator for Mini-Fit Jr.™, Mini-Fit HCS™, and Mini-Fit Plus HCS™ Crimp Terminals, 16 AWG with Large Insulation Diameters	
T2 Terminator™ for insulation OD 2.60-3.15mm optimized for 16 AWG only	<u>0639102800</u>
T2 Terminator™ for insulation OD 2.20-2.45mm optimized for 16 AWG only	<u>0639103000</u>
FineAdjust™	<u>0639015300</u>
Applicator for Insulation OD 1.80-2.20mm Optimized for 16 AWG Only	
<b>Japan</b>	
<b>Description</b>	<b>Product #</b>
Side-Feed Applicator For Full-Auto Machine	<u>0570223200</u>
Applicator for M211A Bench Press, 18-24 AWG Wire	<u>0570223000</u>

This document was generated on 11/21/2016

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**