

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0022284033
Status: Active
Overview: KK® Interconnect System - Molex
Description: KK® 254 Breakaway Header, Vertical, 3 Circuits, 0.38µm Gold (Au) Selective Plating, Mating Pin Length 6.09mm

Documents:

[3D Model](#) [Product Specification PS-10-07-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series 42375
Application Board-to-Board, Signal, Wire-to-Board
Overview KK® Interconnect System - Molex
Product Name KK® 254
UPC 800754320108

Physical

Breakaway Yes
Circuits (Loaded) 3
Circuits (maximum) 3
Color - Resin Black
Durability (mating cycles max) 100
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 0.183/g
Number of Rows 1
Orientation Vertical
PC Tail Length 3.18mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 2.54mm
Plating min - Mating 0.381µm
Plating min - Termination 2.540µm
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable No
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating See Product Specification
Termination Interface: Style Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

42375 Series

Mates With

KK® Crimp Housing 2695 , 6471 , 7880 ,
KK® PC Board Connector 4455

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Engineering Number	42375-0038
--------------------	------------

Reference - Drawing Numbers

Product Specification	PS-10-07-001
Sales Drawing	SD-42375-001

This document was generated on 11/22/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION