

## LEDVANCE® Damp Proof Housing

### Damp-proof luminaire



#### Area of application

- Ideal for industrial and storage facilities
- Car parks and underpasses
- Garages
- Workshops, assembly lines


#### Product benefits

- Prewired for easy installation of tubular AC LED lamps
- Luminous flux and light color dependent of T8 LED lamp selected
- Future-proof solution as compatible with future LED tube generations
- All required accessories included
- Easy installation, no tools required for connection
- Stainless steel clamps with safety screws included

#### Product features

- Luminaire housing: available for 1 and 2 T8 LED lamps
- Type of protection: IP65
- Polycarbonate grey housing, Polycarbonate transparent diffuser
- 5-Years guarantee

Technical data



Product description	GTIN (EAN)	Nominal wattage [W]	Nominal voltage [V]	Power factor [λ]	Luminous flux [lm]	Luminaire efficacy [lm/W]	Colour temperature [K]	CRI index [Ra]
DampProof 1500 1xLamp housing IP65	4058075000988		n/a	n/a	n/a	n/a	n/a	n/a
DampProof 1500 2xLamp housing IP65	4058075001008		n/a	n/a	n/a	n/a	n/a	n/a

Product description	Beam angle	Rated life time L70 / B50 [h]	Type of protection IP rating	Protection class	Product size l x w or Ø [mm]	Height h [mm]	Body colour
DampProof 1500 1xLamp housing IP65	-	n/a	65		1565 x 89	92	grey
DampProof 1500 2xLamp housing IP65	-	n/a	65		1565 x 130	92	grey

Packaging information

Product description	GTIN (EAN)	Dimensions EAN10 l x w x h [mm]	Gross weight EAN 10 [g]	Volume [dm³]	Packaging unit [Pieces/unit]
DampProof 1500 1xLamp housing IP65	4058075000988	1565 x 72 x 86	1228	8.01	12
DampProof 1500 2xLamp housing IP65	4058075001008	1565 x 115 x 86	1445	12.89	8

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.