



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 1.2-10W G4 827

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

Product data


General Information			
Cap base	G4 [G4]	Starting time (nom.)	0.5 s
Nominal lifetime (nom.)	15000 h	Warm-up time to 60% light (nom.)	0.5 s
Switching cycle	50000X	Power factor (nom.)	0.5
Technical type	1.2-10W	Voltage (Nom)	12 V
Light Technical		Temperature	
Luminous flux (nom.)	120 lm	T-Case maximum (nom.)	80 °C
Luminous flux (rated) (nom.)	120 lm	Controls and Dimming	
Colour designation	Warm white (WW)	Dimmable	No
Correlated colour temperature (nom.)	2700 K	Approval and Application	
Luminous efficacy (rated) (nom.)	100.00 lm/W	Energy-saving product	Yes
Colour consistency	<6	Suitable for accent lighting	No
Color rendering index (nom.)	80	Energy efficiency label (EEL)	A++
LLMF at end of nominal lifetime (nom.)	70 %	Energy Consumption kWh/1000 h	2 kWh
Operating and Electrical		Product Data	
Input frequency	50-60 Hz	Full product code	871869657817900
Power (Rated) (Nom)	1.2 W	Order product name	CorePro LEDcapsuleLV 1.2-10W G4 827
Lamp current (nom.)	200 mA	EAN/UPC – product	8718696578179
Wattage equivalent	10 W		

CorePro LEDcapsule LV

Order code	57817900
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	929001244302

Net weight (piece)	0.012 kg
--------------------	----------

Dimensional drawing



Product	D	C
CorePro LEDcapsuleLV 1.2-10W G4 827	14.3 mm	39.2 mm

Capsule 12V 1.2W-10W 105lm 2700K G4 ND

Photometric data

General Uniform Lighting

