



# Classic filament LED Lamps

## CLA LEDBulb D 4.5-40W A60 B22 827 CL

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data


General Information		Power (Rated) (Nom)	
Cap base	B22 [ B22]		4.5 W
Bulb shape	A60 [ A 60mm]	Lamp current (nom.)	29 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	40 W
Switching cycle	20000X	Starting time (nom.)	0.5 s
Technical type	4.5-40W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Luminous flux (nom.)	470 lm	Dimmable	Yes
Luminous flux (rated) (nom.)	470 lm		
Colour designation	Warm white (WW)	Mechanical and Housing	
Correlated colour temperature (nom.)	2700 K	Bulb finish	Clear (CL)
Luminous efficacy (rated) (nom.)	104.44 lm/W		
Colour consistency	<6	Approval and Application	
Color rendering index (nom.)	80	Energy-saving product	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Suitable for accent lighting	No
		Energy efficiency label (EEL)	A++
Operating and Electrical			
Input frequency	50-60 Hz		

## Classic filament LED Lamps

Energy Consumption kWh/1000 h	5 kWh
<b>Product Data</b>	
Full product code	871869657549900
Order product name	CLA LEDBulb D 4.5-40W A60 B22 827 CL
EAN/UPC – product	8718696575499
Order code	57549900

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001228202
Net weight (piece)	0.030 kg

### Dimensional drawing



filament 4.5W-40W 470lm NAD 2700K B22D

Product	D	C
CLA LEDBulb D 4.5-40W A60 B22 827 CL	60 mm	110.5 mm

Photometric data

General Uniform Lighting

