



# SceneSwitch LED Lamps

## LED Scene Switch 60W A60 E27 WW-CW FR ND 1BC/4

Some situations call for cool light, others benefit from the ambiance of a warm cosy glow. With Philips SceneSwitch LED lamps, you can have different light settings from just one bulb, candle or spot. And you don't need a dimmer! Optimise your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

### Product data

General Information	
Cap base	E27 [ E27]
Bulb shape	A60 [ A 60mm]
Nominal lifetime (nom.)	15000 h
Switching cycle	100000X
Technical type	9.5-60W
Technical Type Setting(s)	9.5-60 W

Light Technical	
Luminous flux (nom.)	806 lm
Luminous flux (rated) (nom.)	806 lm
Colour designation	Warm white (WW)
Correlated Color Temperature Setting(s)	2700/4000 K
Luminous efficacy (rated) (nom.)	84.84 lm/W
Colour consistency	<6
Color rendering index (nom.)	80

LLMF at end of nominal lifetime (nom.)	70 %
--	------

Operating and Electrical	
Input frequency	50-60 Hz
Power (Rated) (Nom)	9.5 W
Lamp current (nom.)	100 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No

## SceneSwitch LED Lamps

### Mechanical and Housing

Bulb finish	Frosted (FR)
-------------	--------------

### Approval and Application


Energy-saving product	Yes
Suitable for accent lighting	No
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	9.5 kWh

### Product Data

Full product code	871869659837500
-------------------	-----------------

Order product name	LED Scene Switch 60W A60 E27 WW-CW FR ND 1BC/4
EAN/UPC – product	8718696598375
Order code	59837500
Numerator – quantity per pack	1
Numerator – packs per outer box	4
Material no. (12NC)	929001264101
Net weight (piece)	0.065 kg

### Dimensional drawing



SSW EMEA Color\_9.5W 827-40 800lm E27 ND

Product	D	C
LED Scene Switch 60W A60 E27 WW-CW FR ND 1BC/4	61 mm	111 mm

Photometric data

General Uniform Lighting

