



CorePro LEDluster

Corepro lustre ND 5.5-40W E14 827 P45 CL

The frosted CorePro LEDluster is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E27 or E14 holder. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data


General Information		Warm-up time to 60% light (nom.)	
Cap base	E14 [E14]		instant full light
Bulb shape	P45 [P 45mm]	Power factor (nom.)	0.5
Nominal lifetime (nom.)	15000 h	Voltage (Nom)	220-240 V
Switching cycle	50000X	Temperature	
Technical type	5.5-40W	T-Case maximum (nom.)	95 °C
Light Technical		Controls and Dimming	
Luminous flux (nom.)	470 lm	Dimmable	no
Luminous flux (rated) (nom.)	470 lm	Mechanical and Housing	
Colour designation	Warm white (WW)	Bulb finish	Clear (CL)
Correlated colour temperature (nom.)	2700 K	Approval and Application	
Luminous efficacy (rated) (nom.)	85 lm/W	Suitable for accent lighting	No
Colour consistency	<6	Energy efficiency label (EEL)	A+
Color rendering index (nom.)	80	Energy Consumption kWh/1000 h	6 kWh
LLMF at end of nominal lifetime (nom.)	70 %	Product Data	
Operating and Electrical		Full product code	871869645483100
Input frequency	50-60 Hz	Order product name	Corepro lustre ND 5.5-40W E14 827 P45 CL
Power (Rated) (Nom)	5.5 W	EAN/UPC – product	8718696454831
Lamp current (nom.)	50 mA	Order code	45483100
Wattage equivalent	40 W		
Starting time (nom.)	0.5 s		

CorePro LEDluster

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001142602

Net weight (piece)	0.040 kg
--------------------	----------

Dimensional drawing



LED ND 5.5-40W E14 827 220-240V P45 CL

Product	D	C
Corepro lustre ND 5.5-40W E14 827 P45 CL	45 mm	88 mm

