

EX Series Heatsinks

For TO-220 and TO-247 devices and bridge rectifiers

FEATURES

- Vertical through-hole PCB mounting
- E3A-T220-25E has a 8-32 threaded mounting hole for a bridge rectifier in a D34 type square package
- The thickened side fins can be used to secure the heat sink to a side wall or to mount TO-220's
- Threaded mounting holes



SERIES SPECIFICATIONS


Heatsink Part Number	For Package Type	Ohmite Resistor Series	Surface Area (in ² / mm ²)	Weight (oz. / g)	Thermal Resistance* (°C/W)
E2A-T220-38AE	TO-220	TBH, TCH	7.96 / 5129	0.40 / 11.21	14.0
E2A-T220-25AE	TO-220	TBH, TCH	5.30 / 2419	0.26 / 7.5	16.4
E2A-T247-38AE	TO-247	TEH100	7.95 / 5129	0.40 / 11.21	14.0
E3A-T220-25AE	D34		9.4 / 6064	0.60 / 17.0	12.4

*Natural convection at 5W dissipation

CHARACTERISTICS

Heat sink	Aluminum 6063-T5 or equivalent with either black anodized or degreased finish
Solder feet	steel tin plated
Interface thermal resistance	for improvement, use thermal joint compound or 0.005 Grafoil (TGon 800 by Laird)
Interface electrical isolation	Sil-Pad 900S by Bergquist or equivalent

Heat Dissipation



(continued)


EX Series Heatsinks

For TO-220 and TO-247 devices and bridge rectifiers


DIMENSIONS

in. (mm)


E2A-T220-38AE




E2A-T220-25AE



E2A-T247-38AE



E3A-T220-25AE



ORDERING INFORMATION

Extrusion type RoHS Compliant
E 2 A - T 2 2 0 - 3 8 E
 Series Finish Package Height
 EX A = anodized type