



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 2-20W G4 827

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

Product data


General Information		Starting time (nom.)	
Cap base	G4 [G4]		0.5 s
Nominal lifetime (nom.)	15000 h	Warm-up time to 60% light (nom.)	0.5 s
Switching cycle	50000X	Power factor (nom.)	0.5
Technical type	2-20W	Voltage (Nom)	12 V
Light Technical		Temperature	
Luminous flux (nom.)	200 lm	T-Case maximum (nom.)	80 °C
Luminous flux (rated) (nom.)	200 lm	Controls and Dimming	
Colour designation	Warm white (WW)	Dimmable	No
Correlated colour temperature (nom.)	2700 K	Approval and Application	
Luminous efficacy (rated) (nom.)	100.00 lm/W	Energy-saving product	Yes
Colour consistency	<6	Suitable for accent lighting	No
Color rendering index (nom.)	80	Energy efficiency label (EEL)	A++
LLMF at end of nominal lifetime (nom.)	70 %	Energy Consumption kWh/1000 h	3 kWh
Operating and Electrical		Product Data	
Input frequency	50-60 Hz	Full product code	871869657819300
Power (Rated) (Nom)	2 W	Order product name	CorePro LEDcapsuleLV 2-20W G4 827
Lamp current (nom.)	290 mA	EAN/UPC – product	8718696578193
Wattage equivalent	20 W		

CorePro LEDcapsule LV

Order code	57819300
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	929001244402

Net weight (piece)	0.012 kg
--------------------	----------

Dimensional drawing



Capsule 12V 2W-20W 200lm 2700K G4 ND

Product	D	C
CorePro LEDcapsuleLV 2-20W G4 827	14.3 mm	45 mm

Photometric data

General Uniform Lighting

