



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 2-20W G4 827 D

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

Product data


General Information		Warm-up time to 60% light (nom.)	
Cap base	G4 [G4]		0.5 s
Nominal lifetime (nom.)	15000 h	Power factor (nom.)	0.7
Switching cycle	50000X	Voltage (Nom)	12 V
Technical type	2-20W		
Light Technical		Temperature	
Luminous flux (nom.)	200 lm	T-Case maximum (nom.)	84 °C
Luminous flux (rated) (nom.)	200 lm		
Colour designation	Warm white (WW)	Controls and Dimming	
Correlated colour temperature (nom.)	2700 K	Dimmable	Yes
Luminous efficacy (rated) (nom.)	100.00 lm/W		
Colour consistency	<6	Approval and Application	
Color rendering index (nom.)	80	Energy-saving product	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Suitable for accent lighting	Yes
		Energy efficiency label (EEL)	A++
		Energy Consumption kWh/1000 h	3 kWh
Operating and Electrical		Product Data	
Power (Rated) (Nom)	2 W	Full product code	871869657865000
Lamp current (nom.)	220 mA	Order product name	CorePro LEDcapsuleLV 2-20W G4 827 D
Wattage equivalent	20 W	EAN/UPC – product	8718696578650
Starting time (nom.)	0.5 s	Order code	57865000

CorePro LEDcapsule LV

Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	929001235302

Net weight (piece)	0.012 kg
--------------------	----------

Dimensional drawing



Capsule 12V 2W-20W 200lm 2700K G4 D

Product	D	C
CorePro LEDcapsuleLV 2-20W G4 827 D	17 mm	48 mm

Photometric data

General Uniform Lighting

