



# CorePro LEDspot MV

## CorePro LEDspotMV ND 2.7-40W 827 R63 36D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a E27 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Product data


General Information		Wattage equivalent	
Cap base	E27 [ E27]		40 W
Nominal lifetime (nom.)	15000 h	Starting time (nom.)	0.5 s
Switching cycle	50000X	Warm-up time to 60% light (nom.)	1 s
Technical type	2.7-40W	Power factor (nom.)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Beam Angle (Nom)	36 °	T-Case maximum (nom.)	82 °C
Luminous intensity (nom.)	450 cd		
Colour designation	Warm white (WW)	Controls and Dimming	
Rated beam angle	36 °	Dimmable	No
Correlated colour temperature (nom.)	2700 K		
Luminous efficacy (rated) (nom.)	77.78 lm/W	Approval and Application	
Colour consistency	<6	Energy-saving product	Yes
Color rendering index (nom.)	80	Suitable for accent lighting	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Energy efficiency label (EEL)	A++
Luminous Flux In 90° Cone (Rated)	210 lm	Energy Consumption kWh/1000 h	3 kWh
Operating and Electrical		Product Data	
Input frequency	50-60 Hz	Full product code	871869657859900
Power (Rated) (Nom)	2.7 W	Order product name	CorePro LEDspotMV ND 2.7-40W 827 R63 36D
Lamp current (nom.)	25 mA	EAN/UPC – product	8718696578599

## CorePro LEDspot MV

Order code	57859900
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001233602

Net weight (piece)	0.065 kg
--------------------	----------

### Dimensional drawing




Product	D	C
CorePro LEDspotMV ND 2.7-40W 827 R63 36D	63 mm	102 mm

R63 220-240V 4W-40W 207lm 2700K E27 ND

Photometric data

Accent Lighting - Spots



## CorePro LEDspot MV

